

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301440050](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Safeway Connector, 2 Pole/3 Wire, NEMA 5-15, 125V, Yellow

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family	Wiring Devices
Series	130144
IP Rating	N/A
NEMA Configuration	NEMA 5-15
Overview	Heavy-Duty Industrial Wiring Devices
Product Literature Order No	987650-8068
Product Name	Safeway
Receptacle Type	Single
Specialty	N/A
Type	Connector
UPC	78678894255
Woodhead	Yes

Physical

Flange	No
Flip Lid	No
Gender	Female
Length	N/A
Locking Blade	No
Poles	2-pole/3-wire

Electrical

Cord Type	N/A
Current - Maximum per Contact	15.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	125V

Material Info

Engineering Number 5269YL



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130144 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301440050](#)
Status: **Active**
Overview: [Heavy-Duty Industrial Wiring Devices](#)
Description: Safeway Connector, 2 Pole/3 Wire, NEMA 5-15, 125V, Yellow

Documents:

[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Wiring Devices
Series [130144](#)
IP Rating N/A
NEMA Configuration NEMA 5-15
Overview [Heavy-Duty Industrial Wiring Devices](#)
Product Literature Order No 987650-8068
Product Name Safeway
Receptacle Type Single
Specialty N/A
Type Connector
UPC 78678894255
Woodhead Yes

Physical

Flange No
Flip Lid No
Gender Female
Length N/A
Locking Blade No
Poles 2-pole/3-wire

Electrical

Cord Type N/A
Current - Maximum per Contact 15.0A
GFCI No
Lighted Connector No
Voltage - Maximum 125V

Material Info

Engineering Number 5269YL



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

China RoHS

Search Parts in this Series

[130144 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION