



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



5350 Duplex Recp 20A/125V Side Wire BR

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 5350 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V |
| Weight per unit | 0.1200 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|--------------------|
| amperage rating | 20 |
| connection | Wire Ground |
| indoor/outdoor | Indoor |
| Number of Wires | 3 |
| Outlet Type | Commercial, Indoor |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 14 - 10 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|---|
| Description | DUPLEX RECP 20A/125V SIDE WIRE BR |
| extra long description | P&S CR20 RECEP DUP 20A/125V SIDE WI |
| Long Description | Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V |
| Product Type | Recep Dup 20A/125V Side Wire Brown |
| Special Features | Side wire, Duplex, tri-driver terminal & Mountingscrews |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007119121 |
| Manufacturers Part Number | CR20 |
| UPC | 785007119121 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | Commercial receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.12 |

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | CULUS, UL 498 |