



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5362LA RCPT Dup Hubpro 20A 125V La *Hubbell Wiring Devices*

Catalog Number	5362LA
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Light Almond
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20
connection	Back and Side Wired
Current Rating	20
Dielectric Strength	Withstands 2,000V minimum
Number of Wires	3-Wire
pallet quantity	4500
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	1875
Wire Size	#12 to #10

### Dimensions and Weight

Size	3.28 in x 1.41 in x 1.09 in;Standard Sized Product
------	--

### Descriptions

Description	RCPT DUP HUBPRO 20A 125V LA
extra long description	HWDK 5362LA RCPT, DUP SB, HUBPRO, 2
Long Description	Straight Blade Devices, Receptacles, Duplex, Commercial/Industrial Grade, 2-Pole 3-Wire Grounding, 20A 125V, 5-20R, Light Almond
Product Type	RCPT, Dup SB, Hubpro, 20A 125V, FG , La
Special Features	Self Grounding

### Manufacturer Information

Brand	Hubbell Wiring Devices
Manufacturers Part Number	5362LA
series	Hubbell-PRO

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Standard Duplex



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	0.25

## Uses, Certifications, and Standards

Application	Hubbell-Pro Extra Heavy Duty
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	5-20R
standard	UL File No. E2186, Certified to CSA 22.2, No. 42 File 285, Fed. Spec. W-C-596, NEMA® WD-6 Compliant