



56062 Rechargeable Headlamp W/Work Light, 300 Lumens

Klein Tools

Catalog Number	56062
Manufacturer	Klein Tools
Description	Klein Tools' Rechargeable Hard Hat Headlamp Easily Attaches Directly to A Klein Hard Hat or Klein Tools' Bracketed Strap. When You Need A Stationary Work Light, Simply Mount The Headlamp Onto Any Ferrous Surface With The Convenient Integrated Magnet. This Versatile Led Headlight Provides Three Modes to Fit Your Task: A Bright, 14-Hour Floodlight A Brighter 9-Hour Focused Spotlight, and An Ultra-Bright 300 Lumen Boost Mode. You'LL Know When It'S Time to Recharge The Lamp, Because The Led Lights On The Batte
Weight per unit	N/A
Product Category	Tools & Testers

Features

battery life	Boost Mode: 4 hr; Flood/Low Mode: 14 hr; Spot/High Mode: 9 hr
bulb type	LED
included	Instruction Manual; Rechargeable Lamp, USB Charging Cord
lumens	Boost: 300; Flood/Low: 100; Spot/High: 215
Material	ABS
media	Yes
Number of Batteries	1
Overall Height	2.09" (5.3 cm)
Overall Width	1.42" (3.6 cm)
Temperature Range	Operating/Charging: 32° to 113°F (0° to 45°C); Storage: 14° to 131°F (-10° to 55°C)

Dimensions and Weight

Diameter	—
Overall Length	2.60" (6.6 cm)



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	RECHARGEABLE HEADLAMP W/WORK LIGHT, 300 LUMENS
extra long description	KLEIN 56062 Rechargeable Headlamp a
Features	Klein Tools' rechargeable hard hat headlamp easily attaches directly to a Klein Hard Hat or Klein Tools' bracketed strap. When you need a stationary work light, simply mount the headlamp onto any ferrous surface with the convenient integrated magnet. This versatile LED headlight provides three modes to fit your task: a bright, 14-Hour floodlight a brighter 9-Hour focused spotlight, and an ultra-bright 300 lumen boost mode. You'll know when it's time to recharge the lamp, because the LED lights on the batte
Long Description	Klein Tools' rechargeable hard hat headlamp easily attaches directly to a Klein Hard Hat or Klein Tools' bracketed strap. When you need a stationary work light, simply mount the headlamp onto any ferrous surface with the convenient integrated magnet. This versatile LED headlight provides three modes to fit your task: a bright, 14-Hour floodlight a brighter 9-Hour focused spotlight, and an ultra-bright 300 lumen boost mode. You'll know when it's time to recharge the lamp, because the LED lights on the batte
Product Type	Rechargeable Headlamp and Worklight
Special Features	3 Modes, Magnet, Battery Gauge

Manufacturer Information

Brand	Klein Tools
GTIN	00092644560620
Manufacturers Part Number	56062
UPC	092644560620

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Headlamp with Rechargeable Internal Battery

Packaging

Carton	1
Package	6
Weight	2.6 oz (74 g)
Weight Per each	0

Uses, Certifications, and Standards

Application	Fabric Strap for Klein Headlamps;Head Light;Work Light Headlamp
standard	BC, CE, NR Can, REACH, RoHS