ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



596DC2 1/2" MC CABLE CONN

NSI INDUSTRIES

Catalog Number	596DC2
Manufacturer	NSI INDUSTRIES
Description	Mighty-Seal 1/2" PVC Jacketed MC/TECK Cable Connector
Weight per unit	16.9 (lbs/each)
Product Category	Liquid Tight Fittings

Features

Connector Type	Jacketed MC/TECK
Material	Zinc Die Cast
Number Of Conductors	1 Cable
Angle	180 Deg
Media	Yes

Material, Color, and Finish

Finish	Ball burnish

Dimensions and Weight

Size	1/2

Descriptions

Description	1/2" MC CABLE CONN
Features	Time Saver: Ideal for Parking Decks/Lot Cable, or Teck cable to box or enclosure.
Long Description	Mighty-Seal 1/2" PVC Jacketed MC/TECK Cable Connector
Product Type	1/2 In PVC JCKTD MC Conn
Special Features	Raintight/Concrete-Tight
Extra Long Description	BPT 596-DC2 1/2 IN PVC JCKTD MC CON

Manufacturer Information

Brand	Bridgeport
	Nsi Industries
GTIN	00781747155962
Manufacturers Part Number	596-DC2
UPC	884739

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	CONNECTOR

Trade Size

Trade Size	1/2

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Packaging

Carton	15
Package	60
Weight Per Each	16.9 (lbs/each)

Uses, Certifications, and Standards

Application	Recommended cable types for connecting 10/4 to 8/3 PVC MC cable to box or enclosure diameter .61 - .69. RainTight/ConcreteTight
Standard	cULus


Bridgeport Fittings Inc.
705 Lordship Blvd.
Stratford, CT 06615

Phone: 203-377-5944
Fax: 203-381-3488

Mighty-Seal JMC/Teck Connectors

Images





Download Photo Image Download Dimensional Image

Dimension A in Inches:	1-3/4
Dimension B in Inches:	17-32
Dimension C in Inches:	1-9/32

Application

Recommended cable types for connecting 10/4 to 8/3 PVC MC cable to box or enclosure diameter .61 - .69. RainTight/ConcreteTight

Product Information

Material:	Zinc Die Cast
Finish:	Ball Burnished, Mirror Finish

Certifications & Codes:

Federal Specification Number:	A-A-50552
NEMA Standard:	FB-1
UL File Number:	E20534
UL Standard:	UL-514B
UNSPSC:	39121419
Patent Number:	6,737,584

Catalog ID: 596-DC2

UPC Number: 78174715596

Description: Mighty-Seal® 1/2" PVC Jacketed MC/TECK Cable Connector

Application: Recommended cable types for connecting 10/4 to 8/3 PVC MC cable to box or enclosure diameter .61 - .69. RainTight/ConcreteTight

Trade Size: 1/2

Std Pkg Qty: 60

Unit Qty: 15