



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



60481212FD Encl 60X48X12 N12 FLRMT CH, 3PT LTCH *Cooper B-Line/Cable Tray*

Catalog Number	60481212FD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Ground Mounted Panel Enclosure, 60" Height, 12" Length, 48" Width, Nema 12, Hinged Cover, 12FD Enclosure, Ground Mount, Large Double Door, Ground Mount Legs, Carbon Steel, Oil-Resistant Gasket
Weight per unit	329.7 (lbs/each)
Product Category	20180411063037

Features

dimensions	12.0000 IN X 48.0000 IN X 60.0000 IN
Material	Carbon Steel
Mounting Type	Ground

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	48.00 In Width X 12.00 In Depth X 60.00 In Height
------	---

Descriptions

Description	ENCL 60X48X12 N12 FLRMT CH,3PT LTCH
extra long description	B-LINE 604812-12FD TYPE 12 DBL-DOOR
Features	Eaton's B-Line series JIC wall mount, ground mount and terminal Type 12 panel enclosures are used to house electrical controls and instruments while helping protect them against circulating dust, falling dirt and dripping non-corrosive liquids.
Long Description	Eaton B-Line series ground mounted panel enclosure, 60" height, 12" length, 48" width, NEMA 12, Hinged cover, 12FD enclosure, Ground mount, Large double door, Ground mount legs, Carbon steel, Oil-resistant gasket
Product Type	Type 12 DBL-Door Floor-Standing Enc, Less PNL, 60X48X12
Special Features	Plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051807608
Manufacturers Part Number	604812-12FD
UPC	782051807608

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Type 12 panel enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	329.7

Uses, Certifications, and Standards

Application	Water and Wastewater Systems - Water and Wastewater Systems - OtherMobile Machinery and Equipment - Mobile Machinery and Equipment - OtherElec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMsRail and Rail SystemsStationary Mach Equip In Factory - RoboticsUtility - Substations, Utility Transmission and Distribution
Mounting	Floor, Leg
nema rating	12
standard	UL 508A,NEMA,CSA C22.2.