

| CAT# | A | B | C |
|----------|------|-------|------|
| 631/631i | 1.16 | .400 | 1.06 |
| 632/632i | 1.39 | .400 | 1.30 |
| 633/633i | 1.55 | .520 | 1.52 |
| 634/634i | 1.93 | .560 | 1.95 |
| 635/635i | 2.28 | .720 | 1.18 |
| 636/636i | 2.50 | .730 | 2.64 |
| 637/637i | 3.08 | .920 | 3.27 |
| 638/638i | 3.37 | 1.050 | 3.91 |
| 639/639i | 3.46 | 1.050 | 4.46 |
| 640/640i | 3.75 | 1.050 | 4.99 |

1/2"-1" 1 SCREW
1 1/4"-4" 2 SCREW

EMT CONNECTORS SET SCREW TYPE

• CONCRETE TIGHT WHEN TAPED

ZINC DIE CAST

| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE |
|-------------|-------|--------|----------|-----------|----------|
| 631 | 16290 | 1/2" | 50 | 500 | 35 |
| 632 | 16300 | 3/4" | 25 | 250 | 25 |
| 633 | 16310 | 1" | — | 50 | 30 |
| 634 | 16320 | 1 1/4" | — | 25 | 8 |
| 635 | 16330 | 1 1/2" | — | 25 | 10 |
| 636 | 16340 | 2" | — | 20 | 11 |
| 637* | 16350 | 2 1/2" | — | 12 | 10 |
| 638* | 16360 | 3" | — | 12 | 12 |
| 639* | 16370 | 3 1/2" | — | 10 | 13 |
| 640* | 16380 | 4" | — | 6 | 9 |


*EMT & RIGID



INSULATED THROAT

| | | | | | |
|-------|-------|--------|----|-----|----|
| 631i | 16390 | 1/2" | 50 | 500 | 35 |
| 632i | 16400 | 3/4" | 25 | 250 | 25 |
| 633i | 16410 | 1" | 50 | 200 | 30 |
| 634i | 16420 | 1 1/4" | — | 25 | 8 |
| 635i | 16430 | 1 1/2" | — | 25 | 10 |
| 636i | 16440 | 2" | — | 20 | 11 |
| 637i* | 16450 | 2 1/2" | — | 12 | 10 |
| 638i* | 16460 | 3" | — | 12 | 12 |
| 639i* | 16470 | 3 1/2" | — | 10 | 13 |
| 640i* | 16480 | 4" | — | 6 | 8 |

*EMT & RIGID



| CAT# | A | B |
|------|------|------|
| 641 | 1.53 | 0.93 |
| 642 | 1.92 | 1.16 |
| 643 | 1.00 | 1.44 |
| 644 | 2.52 | 1.84 |
| 645 | 2.85 | 2.05 |
| 646 | 3.41 | 2.51 |
| 647 | 4.21 | 3.30 |
| 648 | 4.67 | 4.01 |
| 649 | 4.85 | 4.52 |
| 650 | 5.47 | 5.01 |

1/2"-1" 2 SCREW
1 1/4"-4" 4 SCREW

EMT COUPLINGS SET SCREW TYPE


• CONCRETE TIGHT WHEN TAPED

ZINC DIE CAST

| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE |
|-------------|-------|--------|----------|-----------|----------|
| 641 | 16490 | 1/2" | 50 | 500 | 35 |
| 642 | 16500 | 3/4" | 25 | 250 | 25 |
| 643 | 16510 | 1" | 50 | 200 | 28 |
| 644 | 16520 | 1 1/4" | — | 25 | 8 |
| 645 | 16530 | 1 1/2" | — | 25 | 15 |
| 646 | 16540 | 2" | — | 20 | 11 |
| 647* | 16550 | 2 1/2" | — | 12 | 9 |
| 648* | 16560 | 3" | — | 12 | 12 |
| 649* | 16570 | 3 1/2" | — | 10 | 12 |
| 650* | 16580 | 4" | — | 6 | 10 |

*EMT & RIGID





| CAT# | A | B | C |
|----------|------|-------|------|
| 631/631i | 1.16 | .400 | 1.06 |
| 632/632i | 1.39 | .400 | 1.30 |
| 633/633i | 1.55 | .520 | 1.52 |
| 634/634i | 1.93 | .560 | 1.95 |
| 635/635i | 2.28 | .720 | 1.18 |
| 636/636i | 2.50 | .730 | 2.64 |
| 637/637i | 3.08 | .920 | 3.27 |
| 638/638i | 3.37 | 1.050 | 3.91 |
| 639/639i | 3.46 | 1.050 | 4.46 |
| 640/640i | 3.75 | 1.050 | 4.99 |

1/2"-1" 1 SCREW
1 1/4"-4" 2 SCREW

EMT CONNECTORS SET SCREW TYPE

• CONCRETE TIGHT WHEN TAPED

ZINC DIE CAST

| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE |
|-------------|-------|--------|----------|-----------|----------|
| 631 | 16290 | 1/2" | 50 | 500 | 35 |
| 632 | 16300 | 3/4" | 25 | 250 | 25 |
| 633 | 16310 | 1" | — | 50 | 30 |
| 634 | 16320 | 1 1/4" | — | 25 | 8 |
| 635 | 16330 | 1 1/2" | — | 25 | 10 |
| 636 | 16340 | 2" | — | 20 | 11 |
| 637* | 16350 | 2 1/2" | — | 12 | 10 |
| 638* | 16360 | 3" | — | 12 | 12 |
| 639* | 16370 | 3 1/2" | — | 10 | 13 |
| 640* | 16380 | 4" | — | 6 | 9 |


*EMT & RIGID



INSULATED THROAT

| | | | | | |
|-------|-------|--------|----|-----|----|
| 631i | 16390 | 1/2" | 50 | 500 | 35 |
| 632i | 16400 | 3/4" | 25 | 250 | 25 |
| 633i | 16410 | 1" | 50 | 200 | 30 |
| 634i | 16420 | 1 1/4" | — | 25 | 8 |
| 635i | 16430 | 1 1/2" | — | 25 | 10 |
| 636i | 16440 | 2" | — | 20 | 11 |
| 637i* | 16450 | 2 1/2" | — | 12 | 10 |
| 638i* | 16460 | 3" | — | 12 | 12 |
| 639i* | 16470 | 3 1/2" | — | 10 | 13 |
| 640i* | 16480 | 4" | — | 6 | 8 |

*EMT & RIGID



| CAT# | A | B |
|------|------|------|
| 641 | 1.53 | 0.93 |
| 642 | 1.92 | 1.16 |
| 643 | 1.00 | 1.44 |
| 644 | 2.52 | 1.84 |
| 645 | 2.85 | 2.05 |
| 646 | 3.41 | 2.51 |
| 647 | 4.21 | 3.30 |
| 648 | 4.67 | 4.01 |
| 649 | 4.85 | 4.52 |
| 650 | 5.47 | 5.01 |

1/2"-1" 2 SCREW
1 1/4"-4" 4 SCREW

EMT COUPLINGS SET SCREW TYPE

• CONCRETE TIGHT WHEN TAPED

ZINC DIE CAST

| TOPAZ CAT # | UPC# | SIZE | UNIT CTN | SHIP CASE | WT/ CASE |
|-------------|-------|--------|----------|-----------|----------|
| 641 | 16490 | 1/2" | 50 | 500 | 35 |
| 642 | 16500 | 3/4" | 25 | 250 | 25 |
| 643 | 16510 | 1" | 50 | 200 | 28 |
| 644 | 16520 | 1 1/4" | — | 25 | 8 |
| 645 | 16530 | 1 1/2" | — | 25 | 15 |
| 646 | 16540 | 2" | — | 20 | 11 |
| 647* | 16550 | 2 1/2" | — | 12 | 9 |
| 648* | 16560 | 3" | — | 12 | 12 |
| 649* | 16570 | 3 1/2" | — | 10 | 12 |
| 650* | 16580 | 4" | — | 6 | 10 |

*EMT & RIGID

