# Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685




## 651411 Led Double Head Security Light W/MS 3K/4K/5K White

*Satco*

| | |
|---|---|
| Catalog Number | 651411 |
| Manufacturer | Satco |
| Description | 20 Watt Led Dual Head Security Flood Light - 9.61 X 7.32 X 7.17 - 80 Cri - 3000K/4000K/5000K CCT - White Finish - Wet Location Rated |
| Weight per unit | 2.8 (lbs/each) |
| Product Category | Lighting |

### Features

| | |
|---|---|
| amperage rating | 0.180 to 0.080 |
| Lamp Type | LED |
| Power Rating | >0.7 |
| Reflector Type | Clear |
| Socket Type | Integrated |
| Voltage Rating | 120 to 277 |

### Material, Color, and Finish

| | |
|---|---|
| fixture material | die-cast aluminum |
| Style | Utility |

### Dimensions and Weight

| | |
|---|---|
| Size | W:9.61 H:7.17 E:7.32 |

### Descriptions

| | |
|---|---|
| Description | LED DOUBLE HEAD SECURITY LIGHT W/MS 3K/4K/5K WHITE |
| extra long description | SAT 65/1411 LED 2 BULLET HEAD SECUR |
| Long Description | 20 Watt LED Dual Head Security Flood Light - 9.61 x 7.32 x 7.17 - 80 CRI - 3000K/4000K/5000K CCT - White Finish - Wet Location Rated |
| Product Type | Led 2 Bullet Head Security LGT |
| Special Features | Warranty: 5-Years ; FCC Compliant: True ; Photo Cell: Built-in Photocell ; Cct Selectable: True ; CCT (Kelvin Temp): 3000K/4000K/5000K ; Hours Rated: 50000 ; Beam Angle (degree): 110 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Clear ; Lens Material: Polycarbonate (PC) ; Operating Temp: -40F to +122F (-40C to +50C) ; Watts: 20W ; Lumens: 2600L/2700L/2900L ; Sensor Coverage Detection Range: 60 Feet ; Sensor Field Of View: 180 degrees |

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

## Manufacturer Information

| | |
|---|---|
| Brand | Satco |
| GTIN | 00045923415586 |
| Manufacturers Part Number | 65/1411 |
| UPC | 045923415586 |

## Taxonomies, Classifications, and Categories

| | |
|---|---|
| Category Description | LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING |

## Packaging

| | |
|---|---|
| Carton | 1 |
| Weight Per each | 2.77 |

## Uses, Certifications, and Standards

| | |
|---|---|
| Application | Outdoor |
| environmental conditions | Wet |
| Frequency Rating | 50/60 |
| standard | cETLus |