Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65220 Led Security Flood W/O Sensor - Black

Satco

Catalog Number	65220
Manufacturer	Satco
Description	Led Security Light - Dual Head Black Finish 4000K
Weight per unit	2.5 (lbs/each)
Product Category	20220131141206

Features

amperage rating	0.200 to 0.072
Ballast Type	Self
Lamp Type	LED
Material	Die Cast Aluminum
Number of Lamps	2
Power Rating	0.9
Reflector Type	Frost
Socket Type	Integrated
Voltage Rating	120 to 277
Warranty	5 Year Limited - Fixtures
Wattage	20

Material, Color, and Finish

fixture material	die-cast aluminum
Style	Utility

Dimensions and Weight

Height	7.63
Length	7.63
Size	L:7.63 W:4.16 H:4.13
Width	4.16

Descriptions

Description	LED SECURITY FLOOD W/O SENSOR - BLACK
extra long description	SATCO 65/220 LED DUAL HEAD SECURITY
Long Description	LED Security Light - Dual Head Black Finish 4000K
Product Type	Led Dual Head Security Light
Special Features	Warranty: 5-Years ; FCC Compliant: True ; Cct Selectable: False ; CCT (Kelvin Temp): 4000K ; Hours Rated: 50000 ; Beam Angle (degree): 50 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Frost ; Lens Material: Glass ; Operating Temp: -30C (-22F) to +50C (+122F) ; Watts: 20W ; Lumens: 1900L

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Nuvo
GTIN	00045923680427
Manufacturers Part Number	65/220
UPC	045923680427

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Commercial LED

Packaging

Carton	1
Weight	2.54
Weight Per each	2.54

Uses, Certifications, and Standards

Application	Outdoor
environmental conditions	Wet
Frequency Rating	50/60
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)
standard	cULus - Certified