



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 65220 Security Light W/O Sensor Black 4000K

Satco

Catalog Number	65220
Manufacturer	Satco
Description	Led Security Light - Dual Head Black Finish 4000K
Weight per unit	2.5 (lbs/each)
Product Category	Security Lights

### Features

Ballast Type	Self
Lamp Type	Light
Material	Die Cast Aluminum
Number of Lamps	2
Socket Type	Hardwired
Voltage Rating	100 to 277
Warranty	5 Year Limited - Fixtures
Wattage	20

### Material, Color, and Finish

fixture material	Die Cast Aluminum
Style	Commercial

### Dimensions and Weight

Height	7.63
Length	7.63
Width	4.16

### Descriptions

Description	SECURITY LIGHT W/O SENSOR BLACK 4000K
extra long description	SATCO 65/220 LED DUAL HEAD SECURITY
Long Description	LED Security Light - Dual Head Black Finish 4000K
Product Type	Led Dual Head Security Light BK 4K
Special Features	Lawful for sale in California ; California T24 Compliant ; Non-Dimmable ; Energy Star: Yes ; IP Rating: IP65 ; Lumens: 1900 ; Operating Temperature: -30C (-22F) to a maximum of +50C (+122F) ; Photocell: No ; Replaceable Light Source: No ; RoHS compliant ; Fixture Material: Die-cast aluminum ; Shade Material: Glass ; CRI: 80 ; Color Temperature: 4000K ; Beam Angle: 50 degrees ; 50000 average rated hours of use ; 5 Year Limited Warranty



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Nuvo
GTIN	00045923680427
Manufacturers Part Number	65/220
UPC	045923680427

## Taxonomies, Classifications, and Categories

Type	Fixtures
------	----------

## Packaging

Carton	1
Weight	2.54
Weight Per each	2.54

## Uses, Certifications, and Standards

Application	Outdoors
Operating Temperature standard	-20C (-4F) to a maximum of +45C (+113F) cULus Wet Listed