



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65221 Security Light W/Sensor Black 4000K

Satco

Catalog Number	65221
Manufacturer	Satco
Description	Led Security Light - Dual Head Black Finish 4000K Motion Sensor
Weight per unit	2.8 (lbs/each)
Product Category	Security Lights

Features

Ballast Type	Self
Lamp Type	Light
Material	Die Cast Aluminum
Number of Lamps	2
Socket Type	Hardwired
Voltage Rating	120
Warranty	5 Year Limited - Fixtures
Wattage	20

Material, Color, and Finish

fixture material	Die Cast Aluminum
Style	Commercial

Dimensions and Weight

Height	7.63
Length	7.63
Width	4.16

Descriptions

Description	SECURITY LIGHT W/SENSOR BLACK 4000K
extra long description	SATCO 65/221 LED DUAL HEAD SECURITY
Long Description	LED Security Light - Dual Head Black Finish 4000K Motion Sensor
Product Type	Led Dual Head Security Light BK 4K MS
Special Features	Lawful for sale in California ; California T24 Compliant ; Non-Dimmable ; Energy Star: Yes ; IP Rating: IP65 ; Lumens: 1900 ; Operating Temperature: -30C (-22F) to a maximum of +50C (+122F) ; Photocell: Has Motion Sensor ; Replaceable Light Source: No ; RoHS compliant ; Fixture Material: Die-cast aluminum ; Shade Material: Glass ; CRI: 80 ; Color Temperature: 4000K ; Beam Angle: 50 degrees ; 50000 average rated hours of use ; 5 Year Limited Warranty



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Nuvo
GTIN	00045923680397
Manufacturers Part Number	65/221
UPC	045923680397

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Fixtures

Packaging

Carton	1
Weight	2.8
Weight Per each	2.8

Uses, Certifications, and Standards

Application	Outdoors
Operating Temperature standard	-30C (-22F) to a maximum of +50C (+122F) cULus Wet Listed