



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



65550 20W Led Vapor Tight Adjustable 3K/4K/5K 2000LM

Satco

Catalog Number	65550
Manufacturer	Satco
Description	Led Adjustable Vapor Tight Fixture - 20W - CCT Selectable 3K/4K/5K - Gray Finish
Weight per unit	5.1 (lbs/each)
Product Category	Lighting

Features

average life	50000
beam angle	210
Lamp Type	LED
lumens	1700 to 2000
Material	Glass and Die-cast Aluminum
Power Source	Hardwired

Material, Color, and Finish

Finish	Gray
--------	------

Dimensions and Weight

Length	4.72
--------	------

Descriptions

Description	20W LED VAPOR TIGHT ADJUSTABLE 3K/4K/5K 2000LM
extra long description	SATCO 65/550 LED ADJUSTABLE VAPOR T
Long Description	LED Adjustable Vapor Tight Fixture - 20W - CCT Selectable 3K/4K/5K - Gray Finish
Product Type	Led Adjustable Vapor Tight
Special Features	Lawful for sale in California ; Warranty: 5 Year Limited - Fixtures ; CCT: 3000K/4000K/5000K ; Dimmable: Non-Dimmable ; Lamp Base: Integrated LED ; DLC Approved: No ; Energy Star: Yes ; ADA Compliant: No ; FCC Compliant: Yes ; Incandescent Equivalent: 125W ; Indoor/Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Frost ; Operating Frequency: 50/60 Hz ; Operating Temperature: -30C (-22F) to +50C (+122F) ; Location Rating: Wet ; Surge Protection: Built-in surge protection - 2KV ; Wattage Selectable: No

Manufacturer Information

Brand	Nuvo
GTIN	00045923653087
Manufacturers Part Number	65/550
UPC	045923653087



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	Vapor Tight

Packaging

Carton	1
Weight Per each	5.1

Uses, Certifications, and Standards

standard	cETLus - Listed
----------	-----------------