



Catalog Number: 6636-GHC1-NK
Item Description: N1 HINGE CVR GUTTER NK
UPC Code: 784572107939


Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Hinge Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 6x6
Straight Section Length: 36
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG# | LABEL# |
|------------------|---------|
| 6636-GHC1-() | 1002943 |
| RC-6636-GHC1-() | 1125051 |
| SPH-663() | 1132575 |


| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|----------------------|
| 1 | 1 | (SEE CHART) | BACK |
| 2 | 1 | (SEE CHART) | TOP |
| 3 | 3 | 1003198 | HINGE |
| 4 | 6 | 1001290 | SCREW, 10-32 X 5/16 |
| 5 | 1 | (SEE CHART) | UL LABEL, WIREWAY |
| 6 | 1 | 1002942 | LABEL, RATING |
| 7 | 2 | 1002880 | BAG ASSY (NOT SHOWN) |



| SUFFIX | BACK # | COVER # |
|--------|---------|---------|
| -SU | 1105202 | 1011994 |
| -SUC | 1128900 | 1128862 |
| -SO | 1128901 | 1128863 |
| -SUNK | 1011992 | 1011994 |
| -NK | 1128914 | 1128863 |
| -SUNKC | 1128915 | 1128862 |





| SUFFIX | FINISH |
|--------|-------------|
| NONE | PAINTED |
| -NP | NOT PAINTED |



NOTE:
1. PLACE BAG ASSY. INSIDE ENCLOSURE (NOT SHOWN).

| REV. | DATE | DESCRIPTION | BY |
|------|----------|---|-----|
| E | 12/13/13 | CHGD QTY #4 WAS 5, #7 WAS 3 (eECR0002639) | SEM |
| D | 8-28-07 | ADDED BACK & COVER CHART ECO. 15946 | DL |
| D1 | 4/10/08 | ADDED CHART & REMOVED NOTE#2 (ECO.17139) | |

| | | |
|--|--------------------|--|
| Material: | 16 GA. STEEL |  General Offices: Kansas City, MO |
| Shear/ Die#: | | |
| Finish: | MILBANK LIGHT GREY | |
| Part Wt.: | | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2" | | Title: HINGE COVER WIREWAY 6 x 6 x 36, TYPE 1 NEMA ENCLOSURE Catalog No.: (SEE CHART) Customer: MILBANK STANDARD Drawing No.: 358-11 |
| Scale: | NTS | Third Angle  |
| Checked By: | | Date: 1-13-06 |
| Drawn By: | DL | Sheet 1 of 1 |



Catalog Number: 6636-GHC1-NK
Item Description: N1 HINGE CVR GUTTER NK
UPC Code: 784572107939


Brand Name: Milbank
Type: Lay In Wireway
Application: Wireway
Standard: UL Listed, Type 1
Cover Type: Hinge Cover
Enclosure: Indoor Enclosure
Nominal Cross Section: 6x6
Straight Section Length: 36
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False




Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG# | LABEL# |
|------------------|---------|
| 6636-GHC1-() | 1002943 |
| RC-6636-GHC1-() | 1125051 |
| SPH-663() | 1132575 |


| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|----------------------|
| 1 | 1 | (SEE CHART) | BACK |
| 2 | 1 | (SEE CHART) | TOP |
| 3 | 3 | 1003198 | HINGE |
| 4 | 6 | 1001290 | SCREW, 10-32 X 5/16 |
| 5 | 1 | (SEE CHART) | UL LABEL, WIREWAY |
| 6 | 1 | 1002942 | LABEL, RATING |
| 7 | 2 | 1002880 | BAG ASSY (NOT SHOWN) |



| SUFFIX | BACK # | COVER # |
|--------|---------|---------|
| -SU | 1105202 | 1011994 |
| -SUC | 1128900 | 1128862 |
| -SO | 1128901 | 1128863 |
| -SUNK | 1011992 | 1011994 |
| -NK | 1128914 | 1128863 |
| -SUNKC | 1128915 | 1128862 |





| SUFFIX | FINISH |
|--------|-------------|
| NONE | PAINTED |
| -NP | NOT PAINTED |



NOTE:
1. PLACE BAG ASSY. INSIDE ENCLOSURE (NOT SHOWN).

| REV. | DATE | DESCRIPTION | BY |
|------|----------|---|-----|
| E | 12/13/13 | CHGD QTY #4 WAS 5, #7 WAS 3 (eECR0002639) | SEM |
| D | 8-28-07 | ADDED BACK & COVER CHART ECO. 15946 | DL |
| D1 | 4/10/08 | ADDED CHART & REMOVED NOTE#2 (ECO.17139) | |

| | | |
|--|--------------------|--|
| Material: | 16 GA. STEEL |  General Offices: Kansas City, MO |
| Shear/ Die#: | | |
| Finish: | MILBANK LIGHT GREY | |
| Part Wt.: | | |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2" | | Title: HINGE COVER WIREWAY 6 x 6 x 36, TYPE 1 NEMA ENCLOSURE Catalog No.: (SEE CHART) Customer: MILBANK STANDARD Drawing No.: 358-11 |
| Scale: | NTS | Third Angle  |
| Checked By: | | Date: 1-13-06 |
| Drawn By: | DL | Sheet 1 of 1 |