



Catalog Number: 6636-GHC1-NK  
Item Description: N1 HINGE CVR GUTTER NK  
UPC Code: 784572107939


Brand Name: Milbank  
Type: Lay In Wireway  
Application: Wireway  
Standard: UL Listed, Type 1  
Cover Type: Hinge Cover  
Enclosure: Indoor Enclosure  
Nominal Cross Section: 6x6  
Straight Section Length: 36  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False




*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CATALOG#	LABEL#
6636-GHC1-( )	1002943
RC-6636-GHC1-( )	1125051
SPH-663( )	1132575


ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK
2	1	(SEE CHART)	TOP
3	3	1003198	HINGE
4	6	1001290	SCREW, 10-32 X 5/16
5	1	(SEE CHART)	UL LABEL, WIREWAY
6	1	1002942	LABEL, RATING
7	2	1002880	BAG ASSY (NOT SHOWN)



SUFFIX	BACK #	COVER #
-SU	1105202	1011994
-SUC	1128900	1128862
-SO	1128901	1128863
-SUNK	1011992	1011994
-NK	1128914	1128863
-SUNKC	1128915	1128862





SUFFIX	FINISH
NONE	PAINTED
-NP	NOT PAINTED



NOTE:  
1. PLACE BAG ASSY. INSIDE ENCLOSURE (NOT SHOWN).

REV.	DATE	DESCRIPTION	BY
E	12/13/13	CHGD QTY #4 WAS 5, #7 WAS 3 (eECR0002639)	SEM
D	8-28-07	ADDED BACK & COVER CHART ECO. 15946	DL
D1	4/10/08	ADDED CHART & REMOVED NOTE#2 (ECO.17139)	

Material:	16 GA. STEEL	 General Offices: Kansas City, MO
Shear/ Die#:		
Finish:	MILBANK LIGHT GREY	
Part Wt.:		
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2*		Title: HINGE COVER WIREWAY 6 x 6 x 36, TYPE 1 NEMA ENCLOSURE Catalog No.: (SEE CHART) Customer: MILBANK STANDARD Drawing No.: <b>358-11</b>
Scale:	NTS	Third Angle 
Checked By:		Date: 1-13-06
Drawn By:	DL	Sheet 1 of 1



Catalog Number: 6636-GHC1-NK  
Item Description: N1 HINGE CVR GUTTER NK  
UPC Code: 784572107939


Brand Name: Milbank  
Type: Lay In Wireway  
Application: Wireway  
Standard: UL Listed, Type 1  
Cover Type: Hinge Cover  
Enclosure: Indoor Enclosure  
Nominal Cross Section: 6x6  
Straight Section Length: 36  
Material: Steel with Powder Coat Finish  
Finish: ANSI 61 Gray  
Knockouts: False




*Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.*

CATALOG#	LABEL#
6636-GHC1-( )	1002943
RC-6636-GHC1-( )	1125051
SPH-663( )	1132575


ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK
2	1	(SEE CHART)	TOP
3	3	1003198	HINGE
4	6	1001290	SCREW, 10-32 X 5/16
5	1	(SEE CHART)	UL LABEL, WIREWAY
6	1	1002942	LABEL, RATING
7	2	1002880	BAG ASSY (NOT SHOWN)



SUFFIX	BACK #	COVER #
-SU	1105202	1011994
-SUC	1128900	1128862
-SO	1128901	1128863
-SUNK	1011992	1011994
-NK	1128914	1128863
-SUNKC	1128915	1128862





SUFFIX	FINISH
NONE	PAINTED
-NP	NOT PAINTED



- 3/4, 1 CONC. K.O. (12)
- 1/2, 3/4 CONC. K.O. (12)
- 1, 1-1/4 CONC. K.O. (6)

NOTE:  
1. PLACE BAG ASSY. INSIDE ENCLOSURE (NOT SHOWN).

REV.	DATE	DESCRIPTION	BY
E	12/13/13	CHGD QTY #4 WAS 5, #7 WAS 3 (eECR0002639)	SEM
D	8-28-07	ADDED BACK & COVER CHART ECO. 15946	DL
D1	4/10/08	ADDED CHART & REMOVED NOTE#2 (ECO.17139)	

Material:	16 GA. STEEL	 General Offices: Kansas City, MO
Shear/ Die#:		
Finish:	MILBANK LIGHT GREY	
Part Wt.:		
Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2"		Title: HINGE COVER WIREWAY 6 x 6 x 36, TYPE 1 NEMA ENCLOSURE  Catalog No.: (SEE CHART) Customer: MILBANK STANDARD Drawing No.: <b>358-11</b>
Scale:	NTS	Third Angle 
Checked By:		Date: 1-13-06
Drawn By:	DL	Sheet 1 of 1