



TRADEMASTER GROUNDING TOGGLE SWITCH

663WG | [Pass & Seymour](#)

FEATURES & BENEFITS

Triple Pole Switch in white, with grounded terminals, is made with a thermoplastic toggle and frame. It has a smooth, quiet toggle action and is made with high-impact resistant construction. 15 amps, 120 volts.

**Available in bulk packs of 90. Add "U" to end of Catalog Number. Example: 663WGU

- Thermoplastic toggle and frame.
- Extra-long strap.
- High-impact resistant construction.
- Side wire #12 and #14 AWG.
- Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- Smooth, quiet toggle action.
- NAFTA-Compliant Residential Wiring Devices are ideal for use on projects subject to the provisions of the Buy American Act.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

Product Series: TradeMaster

Type: Toggle

Number Of Poles: 3-way

Special Features: NAFTA Compliant, Self-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: FSUL WS896

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.090"
Height (US): 3.281"
Width (US): 1.25"

TECHNICAL INFORMATION

Amps: 15A
Volts: 120VAC
Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





TRADEMASTER GROUNDING TOGGLE SWITCH

663WG | [Pass & Seymour](#)

FEATURES & BENEFITS

Triple Pole Switch in white, with grounded terminals, is made with a thermoplastic toggle and frame. It has a smooth, quiet toggle action and is made with high-impact resistant construction. 15 amps, 120 volts.

**Available in bulk packs of 90. Add "U" to end of Catalog Number. Example: 663WGU

- Thermoplastic toggle and frame.
- Extra-long strap.
- High-impact resistant construction.
- Side wire #12 and #14 AWG.
- Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- Smooth, quiet toggle action.
- NAFTA-Compliant Residential Wiring Devices are ideal for use on projects subject to the provisions of the Buy American Act.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

Product Series: TradeMaster

Type: Toggle

Number Of Poles: 3-way

Special Features: NAFTA Compliant, Self-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: FSUL WS896

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 1.090"
Height (US): 3.281"
Width (US): 1.25"

TECHNICAL INFORMATION

Amps: 15A
Volts: 120VAC
Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

