



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 6648GRTNK 6X648" RT No Ko *Unity MFG*

|                  |   |
|------------------|---|
| Catalog Number   | 6648GRTNK   |
| Manufacturer     | Unity MFG   |
| Description      | Unity 6648GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 6 In, 6 In Depth, Length: 48 In, 16 Ga Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, Nema 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UI 50 and UI 870 - Type 3R: Intended For Outdoor Use Primarily to Provide A Degree Of Protection Against Rain, Sleet and Damage From External Ice Formation, Csa C22.2 No. 26 Certified, Type 3R, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and Termi |
| Weight per unit  | 21.0 (lbs/each)   |
| Product Category | Nema Type 3R Trough & Gutter  |

### Features

|           |                  |
|-----------|------------------|
| Knockouts | NO               |
| Material  | Low-Carbon Steel |

### Material, Color, and Finish

|        |                  |
|--------|------------------|
| Color  | Gray             |
| Finish | POLYESTER POWDER |

### Dimensions and Weight

|        |    |
|--------|----|
| Depth  | 6  |
| Length | 48 |
| Width  | 6  |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Description            | 6X648" RT NO KO   |
| extra long description | UNT 6648GRTNK N3R SCREW COVER GUTTE   |
| Long Description       | Unity 6648GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 6 IN, 6 IN Depth, Length: 48 IN, 16 GA Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, NEMA 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And Termi |
| Product Type           | N3R Screw Cover Gutter No K.O. Powder Coated  |
| Special Features       | For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Unity          |
| GTIN                      | 00761515142042 |
| Manufacturers Part Number | 6648GRTNK      |
| UPC                       | 761515142042   |

## Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | STEEL WIRE WAY JUNCTION BOXES          |
| Type                 | GRT Gutter Slip-On Cover Wiring Trough |

## Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 21 |

## Uses, Certifications, and Standards

|                    |  |
|--------------------|--|
| Application        | For Cable And Wire Junction, Distribution And Termination, Houses Runs Of Control And Power Cable  |
| Enclosure standard | NEMA 3R, IP32<br>UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant |