



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 68RCSTBLK Round Recessed Floor Box; Black

*Abb Installation Products, Inc*

Catalog Number	68RCSTBLK
Manufacturer	Abb Installation Products, Inc
Description	Recessed Service Floor Box Cover Kit, Accepts Duplex Receptacles GFI Receptacles and 2 Port Keystone Data Plate, Black, Non-Metallic, For Use With Flush Service Floor Box, 100 Cubic Inches, Opening Diameter 5-5/32 Inches, Base Diameter 6-3/8 Inches, Depth 6 Inches, 3/4 Inch and 1 Inch Conduit Tapping, Plastic, For Power or Communications/Data and Wood Sub-Floor and Raised Floor Applications
Weight per unit	1.3 (lbs/each)
Product Category	Floor Boxes & Accessories

### Features

Knockouts	FALSE
Material	Non-Metallic

### Material, Color, and Finish

Color	Black
-------	-------

### Descriptions

Description	ROUND RECESSED FLOOR BOX; BLACK
extra long description	ABB 68R-CST-BLK ROUND RECESSED COVE
Long Description	Recessed Service Floor Box Cover Kit, Accepts Duplex Receptacles GFI Receptacles and 2 Port Keystone Data Plate, Black, Non-Metallic, For use with Flush Service Floor Box, 100 Cubic Inches, Opening Diameter 5-5/32 Inches, Base Diameter 6-3/8 Inches, Depth 6 Inches, 3/4 Inch and 1 Inch Conduit Tapping, Plastic, For Power or Communications/Data and Wood Sub-Floor and Raised Floor Applications
Product Type	Round Recessed Cover - Black
Special Features	Unique cover provides aesthetic recessed service

### Manufacturer Information

Brand	Steel City
GTIN	00785991044409
Manufacturers Part Number	68R-CST-BLK
UPC	785991044409

### Taxonomies, Classifications, and Categories

Category Description	FLOOR BOXES
Type	Flush Service



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	4
Weight Per each	1.29

## Uses, Certifications, and Standards

Application	For use with 68 P round floor box
standard	UL E11461 / UL E11461