



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



692LA Combo SW 1P 15A120V Pilot LT 1/25 GRD La *Pass & Seymour/Legrand*

Catalog Number	692LA
Manufacturer	Pass & Seymour/Legrand
Description	15 Amps, 120 Volts, Single Pole, Single Pilot Light, Combination Switch, Non-Grounding, Light Almond.
Weight per unit	0.2000 (lbs/each)
Product Category	Combination Devices

Features

action	SP & Pilot Light
actuator	Toggle
amperage rating	15
connection	Side wire, non-grounding
Contact Configuration	N-O
Contact Rating	15 Amp, 120/125 VAC
operating cycles	30000
Poles	1
Voltage Rating	120/125
Wattage	Pilot Light: 1/25

Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------

Descriptions

Description	COMBO SW 1P 15A120V PILOT LT 1/25 GRD LA
extra long description	P&S 692LA COMBO SW 1P 15A120V PILOT
Long Description	15 amps, 120 volts, Single Pole, Single Pilot Light, Combination Switch, Non-Grounding, Light Almond.
Product Type	Combo SW 1P 15A120V Pilot Lite 1/25 La
Special Features	Easily accessible break-off for separate or common feed. Long-life red neon lamp in pilot light rated 1/25 Watt, 125V. Side wire #12 and #14 AWG. Two devices fit into the space of one.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007690163
Manufacturers Part Number	692LA
UPC	785007690163

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Non-Grounding Combination Single Pole Switch & Pilot Light



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	10
Package	50
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	UL20