



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



691TR TR Combo 1P Switch + Recp 15A/120V BN

Pass & Seymour/LeGrand

Catalog Number	691TR
Manufacturer	Pass & Seymour/LeGrand
Description	Our Standard Pass and Seymour Combination Switches Allow You to Add Lights to Any Room In Your Home Without Having to Add or Replace Wall Boxes. This Tamper-Resistant Version Features A Dual Mechanical Shutter System to Help Prevent The Insertion Of Foreign Objects, Making It Much Safer and More Convenient Than Plastic Outlet Caps. For Detailed Tamper-Resistant Receptacle Information, Visit Our Tamper-Resistant Receptacles Page.
Weight per unit	0.2171 (lbs/each)
Product Category	Combination Devices

Features

action	SP & Recptacle
actuator	Toggle
amperage rating	15
connection	Side wire
Contact Configuration	N-O
Contact Rating	120/125 VAC, 15 Amp
operating cycles	30000
Poles	Single Pole
Voltage	120.0 V
Voltage Rating	120/125
Wattage	Electrical power is expressed in Amps and Volts.

Material, Color, and Finish

Color	Brown
-------	-------

Dimensions and Weight

Size	1.32 L x 0.94 W x 4.06 H
------	--------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	TR COMBO 1P SWITCH + RECP 15A/120V BN
extra long description	P&S 691TR TR COMBO 1P SWITCH + REC
Long Description	Our standard Pass and Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.
Product Type	TR Combo 1P Switch + Rec 15A/120V BN
Special Features	Dual mechanical shutter system to help prevent insertion of foreign objects. Easily accessible break-off for separate or common feed. Side wire #12 and #14 AWG. Two devices fit into the space of one. Grounding combination devices meet NEC Requirements.

Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007242454
Manufacturers Part Number	691-TR
UPC	785007242454

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	COMBINATION

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2171

Uses, Certifications, and Standards

Application	Residential/Commercial
environmental conditions	Flammability: UL94 V2
Mounting	WALL
Operating Temperature	Maximum continuous +60°C, minimum -30°C
standard	CULUS, UL20, UL498