



NON-GROUNDING SINGLE-POLE COMBINATION SWITCH & PILOT LIGHT, LIGHT ALMOND

692LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Pole, Single Pilot Light, Combination Switch, 15 amps, 120/125 volts, Light Almond.

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

Type: Combination, Pilot Light

Number Of Poles: 1

Special Features: Non-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UL Listing No: 20; 498

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.94"

Height (US): 3.28"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120VAC
Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





NON-GROUNDING SINGLE-POLE COMBINATION SWITCH & PILOT LIGHT, LIGHT ALMOND

692LA | [Pass & Seymour](#)

FEATURES & BENEFITS

Single Pole, Single Pilot Light, Combination Switch, 15 amps, 120/125 volts, Light Almond.

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond

Type: Combination, Pilot Light

Number Of Poles: 1

Special Features: Non-Grounding

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

UL Listing No: 20; 498

UL Standard: Yes

UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.94"

Height (US): 3.28"

Width (US): 1.32"

TECHNICAL INFORMATION

Amps: 15A

Volts: 120VAC
Volts (AC): 120

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

