



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6RLDG407LM30K90C 6RLD G4 07LM 30K 90CRI 120 FRPC WWH M6 *Lithonia Lighting - Acuity*

Catalog Number	6RLDG407LM30K90C
Manufacturer	Lithonia Lighting - Acuity
Description	With Juno Retrofit 3000K Warm White Led Retrofit Downlight RLD 6-Inch Trim Modules, Upgrading Your Existing 6-Inch Recessed Fixture Is Inexpensive and Nearly As Simple As Replacing An Incandescent Lamp. Modules Feature A White Aluminum Baffle With A Built-In Flange. A Deeply Regressed Diffusing Lens Conceals The Leds From Direct View and Provides Uniform Aperture Luminance.
Weight per unit	1.4 (lbs/each)
Product Category	Lighting

Features

average life	50,000
dimensions	7.625 x 7.625 x 3.25
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
lumens	1000 LM,700 LM
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Plug-In
Shape	Round
Voltage Rating	120
Warranty	5
Wattage	8

Material, Color, and Finish

Color	White
color rendering index (cri)	90
color temperature	3000
Lens Color	WHITE
Lens Material	Polycarbonate

Dimensions and Weight

Height	3.29
Length	7.625
Width	7.625



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Construction	Retrofit
Description	6RLD G4 07LM 30K 90CRI 120 FRPC WWH M6
extra long description	LITH 6RLD G4 07LM 30K 90CRI 120 FRP
Features	Contractor Select
Long Description	With Juno Retrofit 3000K Warm White LED Retrofit Downlight RLD 6-inch trim modules, upgrading your existing 6-inch recessed fixture is inexpensive and nearly as simple as replacing an incandescent lamp. Modules feature a white aluminum baffle with a built-in flange. A deeply regressed diffusing lens conceals the LEDs from direct view and provides uniform aperture luminance.
Product Type	Trim

Manufacturer Information

Brand	JUNO
GTIN	00194994892991
Manufacturers Part Number	6RLD G4 07LM 30K 90CRI 120 FRP
UPC	194994892991

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	Trim

Trade Size

aperture size	6 in
---------------	------

Packaging

Carton	1
Weight	0.94
Weight Per each	1.4

Uses, Certifications, and Standards

Application	Healthcare,Residential,Retrofit
environmental conditions	Indoor
Mounting	Recessed
standard	cULus ClassifiedCA Title 20,CA Title 24,ENERGY STAR,JA8