

# Carlton®

**Outlet Boxes**  
**T&B Catalog Number:**

7074-02-BH

**UPC Number:**


78635852850

**Status:**

Active

**Description:**

4-gang 48 cu.in. brown phenolic outlet box with side bracket, stabilizing bar and #36 clamps bulk packed.



## Features

#36 clamps bulk packed

## Application

Can be installed in the same stud cavity of a shared two-hour wall.

Phenolic boxes may also face opposite directions with only a 3 in. horizontal separation, ideal for multi-family construction.

All phenolic boxes are permissible for use with 90 degree C connectors.

Listed for masonry walls

## General

Material	Non-Metallic
Color	Brown
Wiring System	Non-metallic sheathed cable
Volume (cu.in.)	48
Work	New
Mounting Method	Side bracket and stabilizing bar
Number of Gangs	Four

## Dimension Information

Length (inches)	3 5/16
Width (inches)	7 5/8
Depth (inches)	2 5/8

## Packaging

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	103.5 lbs. per 100

## Application Support

Product Overview-Carlton Brown PH Box- Available on Websites

## Certifications



File Nbr:

E 11461

**For further technical assistance, please contact us...**

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)

# Carlton®

**Outlet Boxes**  
**T&B Catalog Number:**

7074-02-BH

**UPC Number:**

78635852850

**Status:**

Active

**Description:**

4-gang 48 cu.in. brown phenolic outlet box with side bracket, stabilizing bar and #36 clamps bulk packed.

**Features**

#36 clamps bulk packed

**Application**

Can be installed in the same stud cavity of a shared two-hour wall.

Phenolic boxes may also face opposite directions with only a 3 in. horizontal separation, ideal for multi-family construction.

All phenolic boxes are permissible for use with 90 degree C connectors.

Listed for masonry walls

**General**

Material	Non-Metallic
Color	Brown
Wiring System	Non-metallic sheathed cable
Volume (cu.in.)	48
Work	New
Mounting Method	Side bracket and stabilizing bar
Number of Gangs	Four

**Dimension Information**

Length (inches)	3 5/16
Width (inches)	7 5/8
Depth (inches)	2 5/8

**Packaging**

Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	103.5 lbs. per 100

**Application Support**


Product Overview-Carlton Brown PH Box- Available on Websites

**Certifications**



File Nbr:  
 E 11461

**For further technical assistance, please contact us...**



Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)