



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7230V 3/8" STR Flex Connector

Appleton/Oz Gedney

Catalog Number	7230V
Manufacturer	Appleton/Oz Gedney
Description	Straight Conduit Connector, Size: 3/8 In, Connection: Armored Ground Wire X Nonmetallic Sheathed Cable, Conductor Range: 0.34 - 0.63 In, Material: Die-Cast Zinc, Height: 0.63 In, Width: 1 In, Thread Length: 0.44 In, Knockout Size: 1/2 In, S
Weight per unit	0.0800 (lbs/each)
Product Category	BX, MC, Armored Cable Fittings

### Features

connection	Armored Ground Wire X Nonmetallic Sheathed Cable
Material	Die-Cast Zinc

### Dimensions and Weight

Size	3/8
------	-----

### Descriptions

Description	3/8" STR FLEX CONNECTOR
extra long description	APP 7230V 3/8-1/2 IN STRAIGHT BOX C
Long Description	Straight Conduit Connector, Size: 3/8 IN, Connection: Armored Ground Wire X Nonmetallic Sheathed Cable, Conductor Range: 0.34 - 0.63 IN, Material: Die-cast Zinc, Height: 0.63 IN, Width: 1 IN, Thread Length: 0.44 IN, Knockout Size: 1/2 IN, S
Product Type	3/8-1/2 In Straight Box Conn
Special Features	Furnished with locknut; Male hub threads-NPS

### Manufacturer Information

Brand	Appleton
GTIN	00781381772501
Manufacturers Part Number	7230V
UPC	781381772501

### Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	Straight Conduit Connector

### Packaging

Carton	1
Package	50
Weight Per each	0.08



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

For Used To Ground And Secure Nonmetallic Sheathed And  
Service Entrance Cable to Boxes And Enclosures

standard

UL 514B, UL Listed: E14813, CSA Standard: C22.2 No. 18.3, CSA  
Certified: 065178, NEMA FB-1