



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 7250S 2-1/2" Emt Steel Comp Connector

Appleton/Oz Gedney

Catalog Number	7250S
Manufacturer	Appleton/Oz Gedney
Description	Features:2 3/8IN Dia X 3 11/32IN Length, 7/8 In Thread Length, Concretetight, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:2.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Weight per unit	1.8 (lbs/each)
Product Category	Steel Uninsulated Straight Com

### Features

connection	Male NPS Thread
Connector Type	Compression
insulation	Non-Insulated
Material	Steel

### Material, Color, and Finish

Color	Metallic
Finish	Zinc Electro Plated

### Dimensions and Weight

Size	2.5
------	-----

### Descriptions

Description	2-1/2" EMT STEEL COMP CONNECTOR
extra long description	EGS 7250S 2-1/2 IN EMT COMP CONN
Long Description	Features:2 3/8IN Dia X 3 11/32IN Length, 7/8 IN Thread Length, Concretetight, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:2.5IN, Connection:Male NPS Thread, Material:Steel, Finish:Zinc Electro Plated
Product Type	2-1/2 In Emt Comp Conn
Special Features	2 3/8 IN Dia X 3 11/32 IN Length, 7/8 IN Thread Length, Concretetight

### Manufacturer Information

Brand	Appleton
GTIN	00687855874200
Manufacturers Part Number	7250S
UPC	687855874200

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	EMT Conduit Straight Compression Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Trade Size

Trade Size ..... 2.5

## Packaging

Carton ..... 2

Package ..... 10

Weight Per each ..... 1.8

## Uses, Certifications, and Standards

Application ..... To ground and secure EMT Raceways to boxes and enclosures

nema rating ..... FB-1

standard ..... UL Standard: 514B; UL Listed: E14815, E14895; CSA Standard:

C22.2 No. 18.3, cUL Listed: E14815; CSA Certified: 028507;

NEMA: FB-1