



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



74011046 90 Male, DCG, 1.1-1.2", 1.50" W/Mesh *Hubbell Wiring Devices*

Catalog Number	74011046
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, 1.125-1.250", 1.50" With Mesh
Weight per unit	0.7000 (lbs/each)
Product Category	Cable & Cord Grips

Features

Number of Conductors	Single
pallet quantity	240

Material, Color, and Finish

Color	Metallic
-------	----------

Dimensions and Weight

Size	1 1/2" NPT
------	------------

Descriptions

Description	90 MALE, DCG, 1.1-1.2", 1.50" W/MESH
extra long description	HWDK 074011046 90 MALE, DCG, 1.1-1.
Features	Deluxe cord grips help to alleviate pull tension on terminals, control cable arc-of-bend, prevent cord pull-out and provide a Liquidtight seal. They are offered with either aluminum, stainless steel or nylon fittings in a variety of configurations and NPT thread sizes. Additionally, a completely non-metallic product is available. Specific uses are: wiring enclosures, pendant stations, hand tools, construction, processing and material handling equipment, pumps, motors and machine tools.
Long Description	Kellems Wire Management, Deluxe Cord Grips, 90 Degree Male, 1.125-1.250", 1.50" with Mesh
Product Type	90 Male, DCG, 1.1-1.2", 1.50" W/Mesh
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585323008
Manufacturers Part Number	074011046
series	Deluxe Cord Grips
UPC	783585323008



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Watertight Hub, 3-PIECE COUPLINGS, THREADLESS COUPLINGS
AND THREADLESS CONNECTOR

Type 90 Degree Male Thread

Packaging

Carton 2

Package 1

Weight Per each 0.7

Uses, Certifications, and Standards

Application 90 Degree Male- Form 5

environmental conditions Suitable For Use In Wet Locations When Used With A Listed
Sealing Ring Between Box And Fitting.

Mounting Locknut or Tapped Opening

standard UL Listed