



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



752 3/4" Conduit Nipp

Topaz - Southwire LLC

Catalog Number	752
Manufacturer	Topaz - Southwire LLC
Description	Rigid Conduit Nipple, Threaded Male, Hex Head Type; Die-Cast Zinc Material; 0.75 Inch; Imc/Rigid Conduit Used On; Ul, Csa Approval; 1.29 Inch Diameter; 500 Per Case Standard Package; 3/4 Inch Trade Size; Non-Insulated Throat Type
Weight per unit	N/A
Product Category	Rigid Conduit Fittings - Steel

Features

Material	Die-Cast Zinc
Throat Type	Non-Insulated

Dimensions and Weight

Diameter	1.29 Inch
Length	0.75 INCH

Descriptions

Commodity Description	Rigid Conduit Fittings - Steel
Description	3/4" CONDUIT NIPP
extra long description	HEX HEAD TYPE; DIE-CAST ZINC MATERIAL; 0.75 INCH; UL (CANADA AND US), UL 514B APPROVAL; FEDERAL SPECIFICATION W-F-406E/W-F-406D, NEMA FB1-2014 APPLICABLE STANDARD; 500 PER CASE STANDARD PACKAGE; 3/4 INCH TRADE SIZE; MALE THREADED END TYPE; OUTER DIAMETER 1.29 INCH; THROAT TYPE NON-INSULATED; USED ON IMC/RIGID CONDUIT
Long Description	RIGID CONDUIT NIPPLE, THREADED MALE, HEX HEAD TYPE; DIE-CAST ZINC MATERIAL; 0.75 INCH; IMC/RIGID CONDUIT USED ON; UL, CSA APPROVAL; 1.29 INCH DIAMETER; 500 PER CASE STANDARD PACKAGE; 3/4 INCH TRADE SIZE; NON-INSULATED THROAT TYPE
Product Type	Rigid Conduit Nipple

Manufacturer Information

Brand	SOUTHWIRE ROUGH ELECTRICAL COMPONENTS
GTIN	00751338178700
UPC	751338178700

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Threaded Male, Hex Head



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Trade Size	3/4 INCH
------------	----------

Packaging

Carton	1
Package	50
Standard Package	500 PER CASE
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL, CSA
Used On	IMC/RIGID CONDUIT