



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



75454 Stinger DS Led HL Flashlight *Streamlight, Inc.*

Catalog Number	75454
Manufacturer	Streamlight, Inc.
Description	Stinger, Rechargeable Nimh Battery Battery Type, 800 LM Brightness (Lumens), Anodized Finish, 22.48 CM;8.85 In Length, Aluminum Material, IEC Type A Standards Met, 12 V DC;120 V Voltage Rating, 12.8 Oz;364 G Weight
Weight per unit	2.9 (lbs/each)
Product Category	Misc

Features

Battery Included	Yes
Battery Size	Nickel-Metal Hydride
Lamp Type	LED
Number of Batteries	1

Material, Color, and Finish

Body Material	Aluminum
Color	Black

Descriptions

Additional Information	Intensity 800 Lumen; Run Time 5 Hour (Low), 1.5 Hour (High); Beam Distance 310 Meter; Maximum Candela 24000; Includes 120 Volt AC/12 Volt DC Cord
Commodity Description	FLASHLIGHTS,LANTERNS,WARNING LIGHTS
Description	STINGER DS LED HL FLASHLIGHT
extra long description	RECHARGEABLE TYPE; BLACK COLOR; CE APPROVAL; ALUMINUM BODY MATERIAL; LED LAMP TYPE; NICKEL-METAL HYDRIDE BATTERY SIZE; 1 BATTERY(S); YES BATTERY INCLUDED; STINGER DS[R] BRAND; INTENSITY 800 LUMEN; RUN TIME 5 HOUR (LOW), 1.5 HOUR (HIGH); BEAM DISTANCE 310 METER; MAXIMUM CANDELA 24000; INCLUDES 120 VOLT AC/12 VOLT DC CORD

Manufacturer Information

Brand	Streamlight, Inc.
GTIN	00080926754546
UPC	080926754546

Taxonomies, Classifications, and Categories

Category Description	FLASHLIGHTS AND BATTERIES
Type	Rechargeable



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight Per each	2.9033

Uses, Certifications, and Standards

Approval	CE
----------	----