



## ADJUSTABLE FAR-SIDE BOX SUPPORT, PLASTIC, 2 1/8" BOX DEPTH

### CATALOG NUMBER

**766PMD**



### CERTIFICATIONS



### FEATURES

- Prevents boxes from being pushed back into the stud cavity, reducing costly trim out issues
- Easily snaps into existing box holes
- Provides rigid support near the center of the box
- No adjustment needed in a 3-5/8" wall
- Can be stacked or trimmed for any stud wall depth

### PRODUCT ATTRIBUTES

- Material: Acrylonitrile Butadiene Styrene
- Finish: Plain
- Box Depth: 2.12
- Stud Wall Depth: 2 1/2" - 3 1/2"; 3 1/2" Min
- Color: Blue

## ADDITIONAL PRODUCT DETAILS

---

No load rating, for positioning only.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**



## ADJUSTABLE FAR-SIDE BOX SUPPORT, PLASTIC, 2 1/8" BOX DEPTH

### CATALOG NUMBER

---

**766PMD**



### CERTIFICATIONS

---



### FEATURES

---

Prevents boxes from being pushed back into the stud cavity, reducing costly trim out issues

Easily snaps into existing box holes

Provides rigid support near the center of the box

No adjustment needed in a 3-5/8" wall

Can be stacked or trimmed for any stud wall depth

### PRODUCT ATTRIBUTES

---

Material: Acrylonitrile Butadiene Styrene

Finish: Plain

Box Depth: 2.12

Stud Wall Depth: 2 1/2" - 3 1/2"; 3 1/2" Min

Color: Blue

## ADDITIONAL PRODUCT DETAILS

---

No load rating, for positioning only.

## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**