



Commercial grade AC decorator combination switches

Product description


Single-pole, 3-way
15A, 120/277V/AC



7728



7729



TR7730

Decorator combination switches, back & side wire



Rating A	V/AC	Description	Color suffix	Catalog no.	
15	120/277	(2) Single-pole, switches	A, BK, LA, V, W	□ 7728__	✓
		(3) Single-pole, switches	A, BK, LA, V, W	□ 7729__	•
		(2) 3-Way, switches	A, BK, LA, V, W	□ 7731__	•
		(1) Single-pole switch with (1) 3-Way switch	A, BK, LA, V, W	□ 7732__	•

Decorator switch with receptacle, back & side wire



Rating A	V/AC	Description	Color suffix	Catalog no.	
15	120/277	(1) Single-pole with NEMA 5-15,	A, BK, LA, V, W	□ TR7730__	•
15	125	(1) 2-Pole, 3-wire tamper resistant receptacle			•

Accessories for commercial specification grade switches

Description	Catalog no.	
1-Gang, standard size, decorator, 302/304 Stainless steel wallplate	□ 93401	• •
2-Gang, standard size, decorator, 302/304 Stainless steel wallplate	□ 93402	• •
1-Gang, standard size, decorator, unbreakable nylon wallplate, white	□ 5151W	• •



93401



93402



5151W

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), BK (Black), LA (Light Almond), V (Ivory), W (White)



Specification information: 120/277V/AC commercial decorator combination: E-40

Compliances, specifications and availability are subject to change without notice.


Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32


Commercial grade AC decorator combination switches

Product description


Single-pole, 3-way
15A, 120/277V/AC



7728



7729



TR7730

Decorator combination switches, back & side wire



Rating	A	V/AC	Description	Color suffix	Catalog no.	
15	120/277	(2)	Single-pole, switches	A, BK, LA, V, W	□ 7728__	✓
		(3)	Single-pole, switches	A, BK, LA, V, W	□ 7729__	•
		(2)	3-Way, switches	A, BK, LA, V, W	□ 7731__	•
		(1)	Single-pole switch with (1) 3-Way switch	A, BK, LA, V, W	□ 7732__	•

Decorator switch with receptacle, back & side wire



Rating	A	V/AC	Description	Color suffix	Catalog no.	
15	120/277	(1)	Single-pole with NEMA 5-15,	A, BK, LA, V, W	□ TR7730__	✓
15	125	(1)	2-Pole, 3-wire tamper resistant receptacle			•

Accessories for commercial specification grade switches

Description	Catalog no.	
1-Gang, standard size, decorator, 302/304 Stainless steel wallplate	□ 93401	• •
2-Gang, standard size, decorator, 302/304 Stainless steel wallplate	□ 93402	• •
1-Gang, standard size, decorator, unbreakable nylon wallplate, white	□ 5151W	• •



93401



93402



5151W

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), BK (Black), LA (Light Almond), V (Ivory), W (White)



Specification information: 120/277V/AC commercial decorator combination: E-40

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-32

RoHS compliant - Page Q-32