



Catalog Number: 8836-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572109346


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 8x8
Straight Section Length: 36
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.



| CAT. NO. | U/L LABEL |
|---------------|-----------|
| 8836-GSC3R | 1002943 |
| RC-8836-GSC3R | 1125051 |
| SPRSCG-8836 | 1132575 |

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|-------------------------|
| 1 | 1 | 1153345 | BACK WELDMENT |
| 2 | 1 | 1004424 | FRONT |
| 3 | 3 | 1001290 | SCREW, 10-32 X 5/16 |
| 4 | 1 | 1002896 | LABEL, RATING 8x8 GSC3R |
| 5 | 1 | (SEE CHART) | UL LABEL, WIREWAY |



NEMA DWG.: #287

| REV. | DATE | DESCRIPTION | BY |
|------|---------|--|------|
| A2 | 7/19/11 | REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN (ECO #21010) | D.F. |

| | | | | |
|---|--------------------|---|---|-------------------------------------|
| Material: | 16 GA. GALV. STEEL | |  <p>General Offices: Kansas City, MO</p> | |
| Shear/ Die#: | | | | |
| Finish: | MILBANK LIGHT GRAY | | | |
| Part Wt.: | | | | |
| Tolerances: | |  | Title: | SCREW COVER WIREWAY NEMA TYPE 3R |
| Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2* | | | Catalog No.: | (SEE CHART) |
| Scale: | NTS | Checked By: | Customer: | |
| Drawn By: | D.F. | Approved By: | Drawing No.: | 1002632 |
| | | | Date: | 7/19/11 |
| | | | Sheet | 1 of 1 |



Catalog Number: 8836-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572109346


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 8x8
Straight Section Length: 36
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CAT. NO. | U/L LABEL |
|---------------|-----------|
| 8836-GSC3R | 1002943 |
| RC-8836-GSC3R | 1125051 |
| SPRSCG-8836 | 1132575 |

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|-------------------------|
| 1 | 1 | 1153345 | BACK WELDMENT |
| 2 | 1 | 1004424 | FRONT |
| 3 | 3 | 1001290 | SCREW, 10-32 X 5/16 |
| 4 | 1 | 1002896 | LABEL, RATING 8x8 GSC3R |
| 5 | 1 | (SEE CHART) | UL LABEL, WIREWAY |



NEMA DWG.: #287

| REV. | DATE | DESCRIPTION | BY |
|------|---------|--|------|
| A2 | 7/19/11 | REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN (ECO #21010) | D.F. |

| | | | | |
|---|--------------------|--------------|---|-------------------------------------|
| Material: | 16 GA. GALV. STEEL | | <p>General Offices: Kansas City, MO</p> | |
| Shear/ Die#: | | | | |
| Finish: | MILBANK LIGHT GRAY | | | |
| Part Wt.: | | | | |
| Tolerances: | | | Title: | SCREW COVER WIREWAY NEMA TYPE 3R |
| Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X* ±2* | | | Catalog No.: | (SEE CHART) |
| Scale: | NTS | Checked By: | Customer: | |
| Drawn By: | D.F. | Approved By: | Drawing No.: | 1002632 |
| | | | Date: | 7/19/11 |
| | | | Sheet | 1 of 1 |