



Catalog Number: 8848-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572109520


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 8x8
Straight Section Length: 48
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CAT. NO.	U/L LABEL
8848-GSC3R	1002943
RC-8848-GSC3R	1125051
SPRSCG-8848	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	FRONT
3	4	1001290	SCREW, 10-32 X 5/16
4	1	1002896	LABEL, RATING 8x8 GSC3R
5	1	(SEE CHART)	UL LABEL, WIREWAY



NEMA DWG.: #288

SUFFIX	FINISH	K.O.s INSTALLED	WELDMENT NO.	FRONT NO.
NONE	MILBANK	YES	1153346	1004425
-NK	LIGHT GRAY	NO	1153347	
-NP	NONE	YES	1156483	1010782
-NP-NK		NO	1156484	

Material:	16 GA. GALV. STEEL	
Shear/ Die#:		
Finish:	SEE CHART	
Part Wt.:		
Tolerances:	Third Angle	
Unless Specified Otherwise		
X.X	±.1	
X.XX	±.03	
X.XXX	±.015	
X*	±2*	
Scale:	NTS	Checked By:
Drawn By:	D.F.	Approved By:



Title: SCREW COVER WIREWAY
NEMA TYPE 3R

Catalog No.: (SEE CHART)

Customer:

Drawing No.: 1002624

REV.	DATE	DESCRIPTION	BY
B2	11/18/11	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN (ECO #21616)	D.F.



Catalog Number: 8848-GSC3R-NK
Item Description: N3R SCREW CVR GUTTER NK
UPC Code: 784572109520


Brand Name: Milbank
Type: Wiring Trough
Special Features: Key Locking Cylinder Latch Provision,
Sealing Eye Lance
Application: Wireway
Standard: UL Listed, Type 3R
Cover Type: Screw Cover
Enclosure: Outdoor Enclosure
Nominal Cross Section: 8x8
Straight Section Length: 48
Material: Steel with Powder Coat Finish
Finish: ANSI 61 Gray
Knockouts: False



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

CAT. NO.	U/L LABEL
8848-GSC3R	1002943
RC-8848-GSC3R	1125051
SPRSCG-8848	1132575

ITEM	QTY.	PART NUMBER	DESCRIPTION
1	1	(SEE CHART)	BACK WELDMENT
2	1	(SEE CHART)	FRONT
3	4	1001290	SCREW, 10-32 X 5/16
4	1	1002896	LABEL, RATING 8x8 GSC3R
5	1	(SEE CHART)	UL LABEL, WIREWAY



SUFFIX	FINISH	K.O.s INSTALLED	WELDMENT NO.	FRONT NO.
NONE	MILBANK	YES	1153346	1004425
-NK	LIGHT GRAY	NO	1153347	
-NP	NONE	YES	1156483	1010782
-NP-NK		NO	1156484	

NEMA DWG.: #288

REV.	DATE	DESCRIPTION	BY
B2	11/18/11	REDRAW INTO SOLIDWORKS; UPDATE K.O. PATTERN (ECO #21616)	D.F.

Material:	16 GA. GALV. STEEL	
Shear/ Die#:		
Finish:	SEE CHART	
Part Wt.:		
Tolerances:	Third Angle	
Unless Specified Otherwise		
X.X	±.1	
X.XX	±.03	
X.XXX	±.015	
X"	±2"	
Scale:	NTS	Checked By:
Drawn By:	D.F.	Approved By:



Title:	SCREW COVER WIREWAY NEMA TYPE 3R
Catalog No.:	(SEE CHART)
Customer:	
Drawing No.:	1002624
Date:	11/18/11
Sheet	1 of 1