



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



8844XSCHC Encl 8X8X4 N4X SS CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	8844XSCHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 8" Height, 4" Length, 8" Width, Nema 4X, Hinged Cover, 4XSCHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, 304 Stainless Steel, Seamless Poured In-Place Gasket
Weight per unit	5.8 (lbs/each)
Product Category	Nema Types 4 & 4X Metallic Enc

Features

dimensions	4.0000 IN X 8.0000 IN X 8.0000 IN
Material	304 Stainless Steel
Mounting Type	Wall

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	8.00 In Width X 4.00 In Depth X 8.00 In Height
------	--

Descriptions

Description	ENCL 8X8X4 N4X SS CH CLAMP CVR
extra long description	B-LINE 884-4XSCHC TYPE 4X SSL JIC C
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 8" height, 4" length, 8" width, NEMA 4X, Hinged cover, 4XSCHC enclosure, Wall mount, Small single door, External mounting feet, 304 stainless steel, Seamless poured in-place gasket
Product Type	Type 4X SSL Jic Continuous Hinge CVR Enc, 8X8X4
Special Features	Cont. piano hinge, panel mount prov., s.s. doorclamps

Manufacturer Information

Brand	Eaton
GTIN	00782051702996
Manufacturers Part Number	884-4XSCHC
UPC	782051702996

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	5.79

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Safety and Security Systems Ind Facilities & Factories - Facility: Power Distribution and Control Commercial / Institutional Buildings / Structures - Power Distribution and Controls Ind Facilities & Factories - Facility: Critical Power Ind Facilities & Factories - Facility: Automation and Monitoring Commercial / Institutional Buildings / Structures - Critical Power Ind Facilities & Factories - Facility: Lighting and Lighting Controls Ind Facilities & Factories - Industrial F
Mounting	EXTERNAL FEET, WALL
nema rating	4X
standard	CSA C22.2, UL 50, NEMA