



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



885GRY Radiant 15A/125V Duplex Recp Gy

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 885GRY |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Sierraplex Receptacle, 15AMP 125VOLT, Screw Terminal and, Speedwire, Gray |
| Weight per unit | 0.1400 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|-----------------|---------------------|
| gang | 2 |
| indoor/outdoor | Indoor |
| insulation | False |
| media | Yes |
| Mounting Type | Box |
| Number of Gangs | 1.0 |
| orientation | Vertical |
| Outlet Type | Indoor, Residential |
| Poles | Double Pole |
| Voltage | 125.0 V |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|-----------|-------|
| Size | 4.25" |
| Thickness | 1.3" |

Descriptions

| | |
|------------------------|---|
| Description | RADIANT 15A/125V DUPLEX RECP GY |
| extra long description | P&S 885GRY RADIANT 15A/125V DUP REC |
| Long Description | Sierraplex Receptacle, 15amp 125volt, Screw Terminal and, Speedwire, Gray |
| Product Type | Radiant 15A/125V Dup Recept Gry |
| Special Features | High impact resistant, extra long strap, quick loop wire aid, long term blade retention |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007885088 |
| Manufacturers Part Number | 885-GRY |
| UPC | 785007885088 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Outlet |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

Amperage 15.0

Packaging

Carton 10

Package 200

Weight Per each 0.14

Uses, Certifications, and Standards

Application Residential/Commercial

environmental conditions 95% (relative humidity, non-condensing)

Mounting WALL

nema rating 15A

standard CULUS, UL, UL 498