



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



88612CHC Encl 8X8X6 N12 CH Clamp CVR

Cooper B-Line/Cable Tray

Catalog Number	88612CHC
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Jic Panel Enclosure, 8" Height, 6" Length, 8" Width, Nema 12, Hinged Cover, 12CHC Enclosure, Wall Mount, Small Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	6.7 (lbs/each)
Product Category	Nema Types 12 & 13 Metallic En

Features

dimensions	6.0000 IN X 8.0000 IN X 8.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	8.00 In Width X 6.00 In Depth X 8.00 In Height
------	--

Descriptions

Description	ENCL 8X8X6 N12 CH CLAMP CVR
extra long description	B-LINE 886-12CHC TYPE 12 JIC CONTIN
Features	Eaton's B-Line series JIC panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments, but are also commonly used as industrial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series JIC panel enclosure, 8" height, 6" length, 8" width, NEMA 12, Hinged cover, 12CHC enclosure, Wall mount, Small single door, External mounting feet, Carbon steel, Seamless poured in-place gasket
Product Type	Type 12 Jic Continuous Hinge CVR Enc, 8X8X6
Special Features	Cont. piano hinge, panel mount, plated door clamps

Manufacturer Information

Brand	Eaton
GTIN	00782051001334
Manufacturers Part Number	88612CHC
UPC	782051001334

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	JIC panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	6.71

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Lighting and Lighting Controls Commercial / Institutional Buildings / Structures - Critical Power Ind Facilities & Factories - Facility: Lighting and Lighting Controls Ind Facilities & Factories - Mfg. Process Electrification and Control Commercial / Institutional Buildings / Structures - Power Distribution and Control Ind Facilities & Factories - Facility: Safety and Security Systems Ind Facilities & Factories - Facility: Automation and Monitoring Ind Faciliti
Mounting	EXTERNAL FEET, WALL
nema rating	12
standard	CSA C22.2, UL 508A, NEMA