



MILBANK
ENERGY AT WORK



886-SC3R-NK

| | |
|-------------------------------|--|
| Catalog Number | 886-SC3R-NK |
| Marketing Product Description | 8x6x8 Screw Cover Type 3R UL Listed Steel No Knockouts ANSI 61 Gray Quad D Knockout For Lock Emboss Mounting Holes In Back |
| UPC | 784572109582 |
| Length (IN) | 6 |
| Width (IN) | 8 |
| Height (IN) | 8 |
| Weight (LB) | 6.5 |
| Brand Name | Milbank |
| Type | Screw Cover |
| Application | Enclosure for Mounting Electrical Equipment |
| Standard | UL Listed |
| Number Of Outlet | 0 |
| Material | G90 Galvanized Steel with Powder Coat Finish |
| Size | 6L x 8W x 8H |
| Color | ANSI 61 Gray |
| Construction | Welded |
| Cable Entry | No Knockouts |
| Mounting | Wall Mount |
| NEMA Rating | Type 3R |

| | |
|------------|-------------------------------------|
| Hinge Type | No Hinge |
| Top | Drip Shield Top |
| Door | Cover |
| Latch | Cover Secured with Plated Screws |
| Support | Formed and Spot Welded |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



MILBANK
ENERGY AT WORK



886-SC3R-NK

| | |
|-------------------------------|--|
| Catalog Number | 886-SC3R-NK |
| Marketing Product Description | 8x6x8 Screw Cover Type 3R UL Listed Steel No Knockouts ANSI 61 Gray Quad D Knockout For Lock Emboss Mounting Holes In Back |
| UPC | 784572109582 |
| Length (IN) | 6 |
| Width (IN) | 8 |
| Height (IN) | 8 |
| Weight (LB) | 6.5 |
| Brand Name | Milbank |
| Type | Screw Cover |
| Application | Enclosure for Mounting Electrical Equipment |
| Standard | UL Listed |
| Number Of Outlet | 0 |
| Material | G90 Galvanized Steel with Powder Coat Finish |
| Size | 6L x 8W x 8H |
| Color | ANSI 61 Gray |
| Construction | Welded |
| Cable Entry | No Knockouts |
| Mounting | Wall Mount |
| NEMA Rating | Type 3R |

| | |
|------------|-------------------------------------|
| Hinge Type | No Hinge |
| Top | Drip Shield Top |
| Door | Cover |
| Latch | Cover Secured with Plated Screws |
| Support | Formed and Spot Welded |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.