



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 886SCNK 8X8X6 SC No Ko *Unity Manufacturing*

Catalog Number	886SCNK
Manufacturer	Unity Manufacturing
Description	Unity 886SCNK Screw-On Cover Enclosure, 16 Ga Painted Low Carbon Steel, Screw Terminal Connection, Gunsmoke Gray Color, Construction: Formed From Code Gauge, Low Carbon Steel, Keyhole Slotted Cover Allows Plated Screws to Stay In Place, Surface Mounting, No Knockouts, Dimensions: 8 In Width X 6 In Depth X 8 In Height, Enclosure: Nema 1, IP30, C/Us UI 50 and UI 50E - Type 1: Intended For Indoor Use Primarily to Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, Csa C22.2 No. 40 Certifie
Weight per unit	5.0 (lbs/each)
Product Category	Nema Type 1 Metallic Enclosure

### Features

connection	Screw Terminal
Knockouts	NO
Material	Low-Carbon Steel

### Material, Color, and Finish

Color	Gray
-------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Construction	Formed From Code Gauge, Low Carbon Steel, Keyhole Slotted Cover Allows Plated Screws To Stay In Place
Description	8X8X6 SC NO KO
extra long description	UNT 886SCNK N1 SCREW COVER PULL BOX
Long Description	Unity 886SCNK Screw-On Cover Enclosure, 16 GA Painted Low Carbon Steel, Screw Terminal Connection, Gunsmoke Gray Color, Construction: Formed From Code Gauge, Low Carbon Steel, Keyhole Slotted Cover Allows Plated Screws To Stay In Place, Surface Mounting, No Knockouts, Dimensions: 8 IN Width X 6 IN Depth X 8 IN Height, Enclosure: NEMA 1, IP30, C/US UL 50 And UL 50E - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 40 Certifie
Product Type	N1 Screw Cover Pull Box No K.O. Powder Coated
Special Features	Covers have keyhole slots which allow the plated screws to stay in place and make for easy installation; Embossed grounding provision on sizes up to 24 IN x 24 IN x 12 IN; Holes are incorporated into the back of enclosure for easy mounting; Cover is secured to the body with plated hex head combo screws; Protects against contact with enclosed equipment; Thermoset polyester powder coated over phosphatized surface finish; For use as junction and pull boxes

## Manufacturer Information

Brand	Unity
GTIN	00761515222928
Manufacturers Part Number	886SCNK
UPC	761515222928

## Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Screw-On Cover Enclosure

## Packaging

Carton	1
Weight Per each	5

## Uses, Certifications, and Standards

Mounting standard	SURFACE C/US UL 50 And UL 50E - Type 1: Intended For Indoor Use Primarily To Provide A Degree Of Protection Against Limited Amounts Of Falling Dirt, CSA C22.2 No. 40 Certified, IEC 60529, RoHS Compliant
-------------------	---