

## Socket Extenders & Adapters



**92-408**  
Candelabra to Candelabra  
E12 - E12 Extender  
Overall Ext. 5/8"  
75W-120V  
Non-UL



**92-405**  
Candelabra to Intermediate  
E12 - E17 Extender  
Overall Ext. 1/2"  
75W-120V  
Non-UL



**90-1519**  
Candelabra to Medium  
E12 - E26  
Overall Ext. 1"  
75W-120V  
Non-UL



**92-407**  
French to Intermediate  
E14 - E17 Extender  
Overall Ext. 1/2"  
75W-120V  
Non-UL



**90-1801**  
Mogul to Mogul  
E39 - E39 Extender  
4KV - Porcelain  
Overall Ext. 2 3/8" - 2 1/4" Dia.  
1500W-600V



**92-323**  
Medium to Medium  
E26 - E26 Extender  
Phenolic  
Overall Ext. 1"  
660W-250V



**92-324**  
Medium to Medium  
E26 - E26 Extender  
Porcelain  
Overall Ext. 1"  
660W-250V



**90-2589**  
Medium to Medium E26 - E26  
2 Piece Glazed Porcelain Extender  
Overall Ext. 1 1/4"  
660W-250V



**90-446** Brown  
**90-2451** Ivory  
Medium Base  
Pull Chain Current Tap  
660W-125V



**90-2449** Brown  
**90-2450** Ivory  
Medium Base  
Keyless Current Tap  
660W-125V



**90-1121** Brown  
**90-2465** Ivory  
Single to Twin Lampholder  
Overall Height 2 3/4" - Ext. 2"  
660W Max. Total-250V



## Socket Extenders & Adapters



**92-408**  
Candelabra to Candelabra  
E12 - E12 Extender  
Overall Ext. 5/8"  
75W-120V  
Non-UL



**92-405**  
Candelabra to Intermediate  
E12 - E17 Extender  
Overall Ext. 1/2"  
75W-120V  
Non-UL



**90-1519**  
Candelabra to Medium  
E12 - E26  
Overall Ext. 1"  
75W-120V  
Non-UL



**92-407**  
French to Intermediate  
E14 - E17 Extender  
Overall Ext. 1/2"  
75W-120V  
Non-UL



**90-1801**  
Mogul to Mogul  
E39 - E39 Extender  
4KV - Porcelain  
Overall Ext. 2 3/8" - 2 1/4" Dia.  
1500W-600V



**92-323**  
Medium to Medium  
E26 - E26 Extender  
Phenolic  
Overall Ext. 1"  
660W-250V



**92-324**  
Medium to Medium  
E26 - E26 Extender  
Porcelain  
Overall Ext. 1"  
660W-250V



**90-2589**  
Medium to Medium E26 - E26  
2 Piece Glazed Porcelain Extender  
Overall Ext. 1 1/4"  
660W-250V



**90-446** Brown  
**90-2451** Ivory  
Medium Base  
Pull Chain Current Tap  
660W-125V



**90-2449** Brown  
**90-2450** Ivory  
Medium Base  
Keyless Current Tap  
660W-125V



**90-1121** Brown  
**90-2465** Ivory  
Single to Twin Lampholder  
Overall Height 2 3/4" - Ext. 2"  
660W Max. Total-250V

