





GE  
Lighting

**44756 - 909**

GE T5 - Low Voltage; Emergency Building; Emergency Building Light



**GENERAL CHARACTERISTICS**

Lamp Type	Miniature - T & TL Shape
Bulb	T5
Base	Wedge (W2.1x9.5d)
Filament	C-2R
Rated Life	50.0 hrs
Atmosphere	Gas-filled
Primary Application	Low Voltage;Emergency Building;Emergency Building Light

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	38.0
Nominal Initial Lumens per Watt	9
Mean Spherical Candlepower (MSCP)	3.0

**ELECTRICAL CHARACTERISTICS**

Wattage	4.0
Voltage	6.0

**DIMENSIONS**

Maximum Overall Length (MOL)	1.4900 in(37.8 mm)
Bulb Diameter (DIA)	0.625 in(15.9 mm)
Light Center Length (LCL)	0.810 in(20.6 mm)

**PRODUCT INFORMATION**



Product Code	44756
Description	909
ANSI Code	909
Standard Package	Case
Standard Package GTIN	10043168447567
Standard Package Quantity	50
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	50
UPC	043168447560



GE  
Lighting

**44756 - 909**

GE T5 - Low Voltage; Emergency Building; Emergency Building Light



**GENERAL CHARACTERISTICS**

Lamp Type	Miniature - T & TL Shape
Bulb	T5
Base	Wedge (W2.1x9.5d)
Filament	C-2R
Rated Life	50.0 hrs
Atmosphere	Gas-filled
Primary Application	Low Voltage;Emergency Building;Emergency Building Light

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	38.0
Nominal Initial Lumens per Watt	9
Mean Spherical Candlepower (MSCP)	3.0

**ELECTRICAL CHARACTERISTICS**

Wattage	4.0
Voltage	6.0

**DIMENSIONS**

Maximum Overall Length (MOL)	1.4900 in(37.8 mm)
Bulb Diameter (DIA)	0.625 in(15.9 mm)
Light Center Length (LCL)	0.810 in(20.6 mm)

**PRODUCT INFORMATION**

Product Code	44756
Description	909
ANSI Code	909
Standard Package	Case
Standard Package GTIN	10043168447567
Standard Package Quantity	50
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	50
UPC	043168447560