

For Catalog Numbers AN16, AN30, AN40, AN56, AN70, AN80, AN800, CN15, CN35^① and CN55 Contactors and Starters (Size 1, 2)

Description	NEMA Size 1		NEMA Size 2		NEMA Size 3
	Series A1 Part No.	Series B1 Part No.	Series A1 Part No.	Series B1 Part No.	
Renewal Parts Publication Number	20861	22177	20861	22177	20426
Contact Kits					
Two-pole	6-65	6-65	6-65-7	6-65-7	6-43-5
Three-pole	6-65-2	6-65-2	6-65-8	6-65-8	6-43-6
Four-pole	6-65-9	6-65-9	6-65-15	6-65-15	—
Five-pole	6-65-10	6-65-10	6-65-16	6-65-16	—
Magnet Coils					
	Coil Suffix				
120V 60 Hz or 110V 50 Hz	A	9-3285-1	9-3285-1	9-3285-1	9-2756-1 KIT
240V 60 Hz or 220V 50 Hz	B	9-3285-2	9-3285-2	9-3285-2	9-2756-2 KIT
480V 60 Hz or 440V 50 Hz	C	9-3285-3	9-3285-3	9-3285-3	9-2756-3 KIT
600V 60 Hz or 550V 50 Hz	D	9-3285-4	9-3285-4	9-3285-4	9-2756-4 KIT
208V 60 Hz	E	9-3285-9	9-3285-9	9-3285-9	9-2756-5 KIT
277V 60 Hz	H	9-3285-7	9-3285-7	9-3285-7	9-2756-9 KIT
208/240V 60 Hz	J	—	—	—	—
240V 50 Hz	K	9-3285-14	9-3285-14	9-3285-14	9-2756-13 KIT
380–415V 50 Hz	L	9-3285-8	9-3285-8	9-3285-8	—
380V 50 Hz	L	—	—	—	9-2756-12 KIT
415V 50 Hz	M	—	—	—	9-2756-8 KIT
550V 50 Hz	N	—	—	—	9-2756-14 KIT
24V 60 Hz–24V 50 Hz	T	—	—	—	—
24V 60 Hz	T	9-3285-6	9-3285-6	9-3285-6	9-2756-6 KIT
24V 50 Hz	U	9-3285-12	9-3285-12	9-3285-12	9-2756-11 KIT
32V 50 Hz	V	9-3285-10	9-3285-10	9-3285-10	9-2756-10 KIT
48V 60 Hz	W	9-3285-11	9-3285-11	9-3285-11	9-2756-15 KIT
48V 50 Hz	Y	9-3285-13	9-3285-13	9-3285-13	9-2756-7 KIT
Magnet Frame Armature					
Lower magnet frame		17-18200	17-18200	17-18200	17-8955-2 KIT
Upper magnet frame		48-1936	48-1936	48-1936	48-1902 KIT

Note

^① CN35A = Size 00, CN35B and CN35D = Size 0, CN35G = Size 2, CN35K = Size 3, CN35N = Size 4, and CN35S = Size 5.

For Catalog Numbers AN16, AN30, AN40, AN56, AN70, AN80, AN800, CN15, CN35^① and CN55 Contactors and Starters (Size 1, 2)

Description	NEMA Size 1		NEMA Size 2		NEMA Size 3	
	Series A1 Part No.	Series B1 Part No.	Series A1 Part No.	Series B1 Part No.		
Renewal Parts Publication Number	20861	22177	20861	22177	20426	
Contact Kits						
Two-pole	6-65	6-65	6-65-7	6-65-7	6-43-5	
Three-pole	6-65-2	6-65-2	6-65-8	6-65-8	6-43-6	
Four-pole	6-65-9	6-65-9	6-65-15	6-65-15	—	
Five-pole	6-65-10	6-65-10	6-65-16	6-65-16	—	
Magnet Coils						
	Coil Suffix					
120V 60 Hz or 110V 50 Hz	A	9-3285-1	9-3285-1	9-3285-1	9-3285-1	9-2756-1 KIT
240V 60 Hz or 220V 50 Hz	B	9-3285-2	9-3285-2	9-3285-2	9-3285-2	9-2756-2 KIT
480V 60 Hz or 440V 50 Hz	C	9-3285-3	9-3285-3	9-3285-3	9-3285-3	9-2756-3 KIT
600V 60 Hz or 550V 50 Hz	D	9-3285-4	9-3285-4	9-3285-4	9-3285-4	9-2756-4 KIT
208V 60 Hz	E	9-3285-9	9-3285-9	9-3285-9	9-3285-9	9-2756-5 KIT
277V 60 Hz	H	9-3285-7	9-3285-7	9-3285-7	9-3285-7	9-2756-9 KIT
208/240V 60 Hz	J	—	—	—	—	—
240V 50 Hz	K	9-3285-14	9-3285-14	9-3285-14	9-3285-14	9-2756-13 KIT
380–415V 50 Hz	L	9-3285-8	9-3285-8	9-3285-8	9-3285-8	—
380V 50 Hz	L	—	—	—	—	9-2756-12 KIT
415V 50 Hz	M	—	—	—	—	9-2756-8 KIT
550V 50 Hz	N	—	—	—	—	9-2756-14 KIT
24V 60 Hz–24V 50 Hz	T	—	—	—	—	—
24V 60 Hz	T	9-3285-6	9-3285-6	9-3285-6	9-3285-6	9-2756-6 KIT
24V 50 Hz	U	9-3285-12	9-3285-12	9-3285-12	9-3285-12	9-2756-11 KIT
32V 50 Hz	V	9-3285-10	9-3285-10	9-3285-10	9-3285-10	9-2756-10 KIT
48V 60 Hz	W	9-3285-11	9-3285-11	9-3285-11	9-3285-11	9-2756-15 KIT
48V 50 Hz	Y	9-3285-13	9-3285-13	9-3285-13	9-3285-13	9-2756-7 KIT
Magnet Frame Armature						
Lower magnet frame		17-18200	17-18200	17-18200	17-18200	17-8955-2 KIT
Upper magnet frame		48-1936	48-1936	48-1936	48-1936	48-1902 KIT

Note

① CN35A = Size 00, CN35B and CN35D = Size 0, CN35G = Size 2, CN35K = Size 3, CN35N = Size 4, and CN35S = Size 5.