

4" Dia. Round Outlet:

Residential Units

Series 9350-HN



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-HN	"HN" hanger, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10460	50	29
22.5	9350-HNK*	"HN" hanger, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10462	50	29

Series 9350-UB



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-UB	Universal bar hanger, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10440	50	43
22.5	9350-UBC2	Universal bar hanger, 2 wire clamps – factory installed	2-3/8	4	50 lb.	10432	50	44
22.5	9350-UBK*	Universal bar hanger, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10450	50	43

Series 9350-UBG



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-UBG	Universal bar hanger, ground strap, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10433	50	44
22.5	9350-UBGK*	Universal bar hanger, ground strap, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10435	50	44

9350-UBKV



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9350-UBKV	Universal bar hanger, Speed Klamps™ – factory installed, energy efficient vapor seal	2-3/8	4	50 lb.	10467	24	22

Series 9351-N



Cu. In. Volume	Catalog Number	Component Description	D	W	Fixture Rating	UPC# 85339	Std. Pkg. Qty.	Std. Pkg. Wt. (lb.)
22.5	9351-N	Fetter ring nails, Speed Klamps™ – bulk packed	2-3/8	4	50 lb.	10475	50	24
22.5	9351-NC2	Fetter ring nails, 2 wire clamps – factory installed	2-3/8	4	50 lb.	65190	50	25
22.5	9351-NK*	Fetter ring nails, Speed Klamps™ – factory installed	2-3/8	4	50 lb.	10476	50	25



* Indicates model shown • See page 7 for Attachment Coding descriptions

