

## OTHER PRODUCTS

### RectorSeal® Duct Seal

Gray putty compound

Code	Description	Qty.
81880	1 lb.	10
81881	5 lbs.	2



#### FEATURES

- Asbestos free
- Air / water tight seal
- Resistant to water, alcohols, mild acids & bases
- Non-corrosive / non-irritant
- Paintable

**Application** • Permanently soft, non-toxic, putty-type compound which adheres to most clean, dry surfaces

- Can be hand applied from 25°F to 120°F

#### Recommended for

- Sealing around the ends of electrical conduits and boxes
- Flashings
- Service mast entries



### Dark Cutting Oil

Low rpm machine thread cutting oil

Code	Description	Qty.
94392	1 qt.	12
94272	1 gal.	6
94192	5 gal.	1
94111	55 gal.	1

#### FEATURES

- Increased lubricity/longer die life
- Penetrates quickly
- Keeps dies cool

**Application** • Designed to reduce friction

- Effective coolant and anti-weld agent
- An extreme pressure lubricant during thread cutting operations
- Will not congeal above 20°F



### Copper-Rich™

High temperature anti-seize and lubricant

Code	Description	Qty.
72851	8 oz.	12
72841	1 lb.	12

#### FEATURES

- Highly conductive
- Exceeds military spec MIL-A-907E

**Application** • Pure micro-sized copper flakes dispersed in a non-melt, high temperature grease

- Resists seizure
- Color: copper

#### Recommended for

- All metal connections including stainless steel to 1800°F
- Ideal for use where electrical conductivity is important



## OTHER PRODUCTS

### RectorSeal® Duct Seal

Gray putty compound

Code	Description	Qty.
81880	1 lb.	10
81881	5 lbs.	2



#### FEATURES

- Asbestos free
- Air / water tight seal
- Resistant to water, alcohols, mild acids & bases
- Non-corrosive / non-irritant
- Paintable

**Application** • Permanently soft, non-toxic, putty-type compound which adheres to most clean, dry surfaces

- Can be hand applied from 25°F to 120°F

#### Recommended for

- Sealing around the ends of electrical conduits and boxes
- Flashings
- Service mast entries



### Dark Cutting Oil

Low rpm machine thread cutting oil

Code	Description	Qty.
94392	1 qt.	12
94272	1 gal.	6
94192	5 gal.	1
94111	55 gal.	1

#### FEATURES

- Increased lubricity/longer die life
- Penetrates quickly
- Keeps dies cool

**Application** • Designed to reduce friction

- Effective coolant and anti-weld agent
- An extreme pressure lubricant during thread cutting operations
- Will not congeal above 20°F



### Copper-Rich™

High temperature anti-seize and lubricant

Code	Description	Qty.
72851	8 oz.	12
72841	1 lb.	12

#### FEATURES

- Highly conductive
- Exceeds military spec MIL-A-907E

**Application** • Pure micro-sized copper flakes dispersed in a non-melt, high temperature grease

- Resists seizure
- Color: copper

#### Recommended for

- All metal connections including stainless steel to 1800°F
- Ideal for use where electrical conductivity is important

