



AQUAGUARD® SENSORS



AG-1100+

Magnetic Float Switch System for Metal Pans

Code	Description	Qty.
96100	Float Switch	30



FEATURES

- Easy, Drill-Free Installation
- Pull Up Test Knob
- Protective Cover
- UL 508 Approved

US Patent
7,710,283

Application • The AG-1100+ is incredibly easy to install. It can be mounted to the drain pan in 10 seconds or less. Installation does not require any pre-drilling for screws. The AG-1100+ incorporates a protective cover to keep out insulation and debris that could prevent the float from rising.

- Normally Open 3rd Wire for Optional External Alarm, Digital Controller, or Energy Management System • Residential and Commercial • High Capacity 5 Amp, 24Volt AC Magnetic Float Switch



AG-1200+

Magnetic Float Switch System for Metal & Plastic Pans

Code	Description	Qty.
96106	Float Switch	30



FEATURES

- Easy, Drill-Free Installation
- Pull Up Test Knob
- Protective Cover
- UL 508 Approved

US Patent
7,710,283

Application • The AG-1200+ has all of the features of the 1100+ plus an innovative two-piece clamp design which allows it to be mounted to a metal secondary drain pan (without a lip) or a plastic secondary drain pan (with a lip) in 10 seconds or less, without screws or drilling. Protective cover keeps out insulation, pests and debris.

- Normally Open 3rd Wire for Optional External Alarm, Digital Controller, or Energy Management System • Residential and Commercial • High Capacity 5 Amp, 24Volt AC Magnetic Float Switch



Condensate Management

Compressor Maintenance

Air Diffusers

Linesets & Lineset Covers

Locking Refrigerant Caps

Equipment Mounting

Specialty Chemicals

Air Conditioning Chemicals

Heating Chemicals

Other Related Products



AQUAGUARD® SENSORS



AG-1100+

Magnetic Float Switch System for Metal Pans

Code	Description	Qty.
96100	Float Switch	30



FEATURES

- Easy, Drill-Free Installation
- Pull Up Test Knob
- Protective Cover
- UL 508 Approved

US Patent
7,710,283

Application • The AG-1100+ is incredibly easy to install. It can be mounted to the drain pan in 10 seconds or less. Installation does not require any pre-drilling for screws. The AG-1100+ incorporates a protective cover to keep out insulation and debris that could prevent the float from rising.

- Normally Open 3rd Wire for Optional External Alarm, Digital Controller, or Energy Management System • Residential and Commercial • High Capacity 5 Amp, 24Volt AC Magnetic Float Switch



AG-1200+

Magnetic Float Switch System for Metal & Plastic Pans

Code	Description	Qty.
96106	Float Switch	30



FEATURES

- Easy, Drill-Free Installation
- Pull Up Test Knob
- Protective Cover
- UL 508 Approved

US Patent
7,710,283

Application • The AG-1200+ has all of the features of the 1100+ plus an innovative two-piece clamp design which allows it to be mounted to a metal secondary drain pan (without a lip) or a plastic secondary drain pan (with a lip) in 10 seconds or less, without screws or drilling. Protective cover keeps out insulation, pests and debris.

- Normally Open 3rd Wire for Optional External Alarm, Digital Controller, or Energy Management System • Residential and Commercial • High Capacity 5 Amp, 24Volt AC Magnetic Float Switch



Condensate Management

Compressor Maintenance

Air Diffusers

Linesets & Lineset Covers

Locking Refrigerant Caps

Equipment Mounting

Specialty Chemicals

Air Conditioning Chemicals

Heating Chemicals

Other Related Products