ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



9794 1-1/4" KNOCK OUT INSULATING BUSHING

NSI INDUSTRIES

Catalog Number	9794
Manufacturer	NSI INDUSTRIES
Description	Insulating Bushing, 1-1/4 in Trade Size, Black, Straight Connection Orientation, Threaded Connection, 1.875 in Width, 0.453 in Height, 1-7/8 in Diameter, +150 °C Operating Temperature, 0.016 lb/EA
Weight per unit	0.0160 (lbs/each)
Product Category	Plastic

Features

Material	Plastic

Material, Color, and Finish

Color	Black
Finish	Natural

Dimensions and Weight

Size	1-1/4

Descriptions

Description	1-1/4" KNOCK OUT INSULATING BUSHING
Long Description	Bushing, Insulating, Plastic Rated 105 Degrees C, 1.750 Inch Hole Dia.
Product Type	1-1/4 In Plastic Knockout Bushin, Box Of 50
Special Features	K.O Dia - 1.734"
Extra Long Description	BPT 9794 1-1/4 IN Plastic Knockout

Manufacturer Information

Brand	Bridgeport
	Nsi Industries
GTIN	00781747007940
UPC	884739

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	BUSHING

Packaging

Carton	50
Package	500
Weight Per Each	0.0160 (lbs/each)

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Uses, Certifications, and Standards

Application	Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.
Temperature Rating	105?°C
Standard	CSA, UL


Bridgeport Fittings Inc.
705 Lordship Blvd.
Stratford, CT 06615

Phone: 203-377-5944
Fax: 203-381-3488

Insulating Bushings - Knockout

Images





Download Photo Image Download Dimensional Image

Dimension A in Inches:	1-3/8
Dimension B in Inches:	1-7/8
Dimension C in Inches:	1-3/4

Application

Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

Product Information

Material:	Plastic
Finish:	Natural

Certifications & Codes:

CSA File Number:	LR24719
NEMA Standard:	FB-1
UL Standard:	UL-514B
UNSPSC:	39121312

Catalog ID: 9794

UPC Number: 781747007940

Description: Bushing, Insulating, Plastic Rated 105 Degrees C, 1.750 Inch Hole Dia.

Application: Converts metallic box rough edged knockout holes to smooth insulated holes for protection of electrical and telecommunications cable. Rated 105 Degrees C.

Trade Size: 1-1/4"

Country of Manufacture: USA

Std Pkg Qty: 500

Unit Qty: 50