



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **A06SA6 120VPRI-6000V Ign.XFMR**

*Dongan Electric MFG. CO.*

|                  |                                                                                                                                                                                                                                                                                                           |
|------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | A06SA6                                                                                                                                                                                                                                                                                                    |
| Manufacturer     | Dongan Electric MFG. CO.                                                                                                                                                                                                                                                                                  |
| Description      | Oil and Gas Ignition Transformer, 60 HZ Frequency Rating, 120 V Input Voltage Rating, Made In Usa, 6000 V Output Voltage Rating, 4.31 In Overall Height, 6.75 In Overall Length, 4.44 In Overall Width, 175 Va Power Rating, Culus Listed, Industrial Gas & Oil Series Power Transformer Transformer Type |
| Weight per unit  | 9.0 (lbs/each)                                                                                                                                                                                                                                                                                            |
| Product Category | Distribution Transformers                                                                                                                                                                                                                                                                                 |

### **Features**

|                |              |
|----------------|--------------|
| dimensions     | 5" X 5" X 5" |
| duty cycle     | 100%         |
| Voltage Rating | 6k Im        |

### **Descriptions**

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | 120VPRI-6000V IGN.XFMR              |
| extra long description | DONGAN A06-SA6 175VA 120 6,000 60HZ |
| Special Features       | Furnaces                            |

### **Manufacturer Information**

|                           |                          |
|---------------------------|--------------------------|
| Brand                     | Dongan Electric MFG. CO. |
| GTIN                      | 00782490120207           |
| Manufacturers Part Number | A06-SA6                  |
| UPC                       | 782490120207             |

### **Taxonomies, Classifications, and Categories**

|                      |                          |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type                 | Ignition Transformer     |

### **Packaging**

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 9 |

### **Uses, Certifications, and Standards**

|           |        |
|-----------|--------|
| Enclosure | NEMA 1 |
|-----------|--------|