



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A200M4CAD SZ4 135A 3P Non Rev Starter Freedom Series

Eaton Corp

Catalog Number	A200M4CAD
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, 120V/60 HZ or 110V/50 HZ Coil Voltage, Size 4, 40 HP At 208V, 50 HP At 240V, 100 HP At 480, 600V, A200 Series, Ambient Compensated Overload Relay With Auto-Reset, Non-Reversing Starter, 135A, 3-Pole
Weight per unit	115.0 (lbs/each)
Product Category	Nema Non-Combination Starters

Features

dimensions 6.7500 IN X 4.6300 IN X 9.9400 IN

Descriptions

Description	SZ4 135A 3P NON REV STARTER FREEDOM SERIES
extra long description	ETN A200M4CAD A 200M4CAD
Features	All Class A200 non-reversing starters utilize Type B three-pole overload relays with optional Type A for auto reset applications. Sizes 5 and 6 include the needed current transformers. Moving and stationary contacts are front accessible for simple and easy inspection and maintenance. All Class A200 starters are UL listed and recognized and are CSA certified.
Long Description	Eaton Freedom NEMA motor control starter, 120V/60 Hz or 110V/50 Hz coil voltage, Size 4, 40 hp at 208V, 50 hp at 240V, 100 hp at 480,600V, A200 series, Ambient Compensated Overload Relay with Auto-Reset, Non-Reversing Starter, 135A, 3-pole
Product Type	A 200m4cad

Manufacturer Information

Brand	Eaton Corp
GTIN	00786678007205
Manufacturers Part Number	A200M4CAD
UPC	786678007205

Taxonomies, Classifications, and Categories

Category Description	FREEDOM/NEMA STYLE
Type	Motor Control

Packaging

Carton	1
Weight Per each	115



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

standard

CSA Certified,UL Listed