Fittings and Brackets

Z Shape Fittings



CAT. NO. A209
For attaching "A" series channel.



CAT. NO. B209
For attaching "B" series channel.



CAT. NO. C209
For attaching "C" series channel.



CAT. NO. CZ209
For attaching "A" back to back.



CAT. NO. EZ209
For attaching "E" series channel.

Standard Dimensions

- Hole Spacing: 1³⁄₁₆" From End
- Hole Spacing: 1⅞" Centers
- Hole Size: 1" Diameter
- Material: 1⅝" Width
- Material: ¼" Thick

Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish

Wing Shape Fittings



CAT. NO. A217



CAT. NO. A218



CAT. NO. AW204



CAT. NO. AW205 L



CAT. NO. AW205-R



CAT. NO. AW214



CAT. NO. AW219



CAT. NO. AW220



CAT. NO. AW224



CAT. NO. AW226



CAT. NO. AW228

Standard Dimensions

- Hole Spacing: 1³⁄₁₆" From End
- Hole Spacing: 1⅞" Centers
- Hole Size: 1" Diameter
- Material: 1⅝" Width
- Material: ¼" Thick

Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish

Thomas&Betts

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

www.tnb.com

Fittings and Brackets

Z Shape Fittings



CAT. NO. A209
For attaching "A" series channel.



CAT. NO. B209
For attaching "B" series channel.



CAT. NO. C209
For attaching "C" series channel.



CAT. NO. CZ209
For attaching "A" back to back.



CAT. NO. EZ209
For attaching "E" series channel.

Standard Dimensions

- Hole Spacing: 1³⁄₁₆" From End
- Hole Spacing: 1⅞" Centers
- Hole Size: 1" Diameter
- Material: 1⅝" Width
- Material: ¼" Thick

Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish

Wing Shape Fittings



CAT. NO. A217



CAT. NO. A218



CAT. NO. AW204



CAT. NO. AW205 L



CAT. NO. AW205-R



CAT. NO. AW214



CAT. NO. AW219



CAT. NO. AW220



CAT. NO. AW224



CAT. NO. AW226



CAT. NO. AW228

Standard Dimensions

- Hole Spacing: 1³⁄₁₆" From End
- Hole Spacing: 1⅞" Centers
- Hole Size: 1" Diameter
- Material: 1⅝" Width
- Material: ¼" Thick

Standard Finish – GoldGalv®, unless otherwise stated.
Add EG suffix for SilverGalv® Finish

Thomas&Betts

United States
Tel: 901.252.8000
800.816.7809
Fax: 901.252.1354

Technical Services
Tel: 888.862.3289

www.tnb.com