



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A200M3CAC A200 - Starter Size 3 Open 3 Pole 120V/60HZ Coil

Eaton Corp

Catalog Number	A200M3CAC
Manufacturer	Eaton Corp
Description	Eaton Freedom Nema Motor Control Starter, Non-Reversing Starter, 120V/60 HZ or 110V/50 HZ Coil Voltage, 90A, Three-Pole, Size 3, 25 HP At 208V, 30 HP At 240V, 50 HP At 480, 600V, A200 Series, Wired For Separate Control
Weight per unit	9.9 (lbs/each)
Product Category	Nema Non-Combination Starters

Features

dimensions 6.7500 IN X 4.6300 IN X 6.9000 IN

Descriptions

Description	A200 - STARTER SIZE 3 OPEN 3 POLE 120V/60HZ COIL
extra long description	ETN A200M3CAC NEMA size 3 starter,
Features	All Class A200 non-reversing starters utilize Type B three-pole overload relays with optional Type A for auto reset applications. Sizes 5 and 6 include the needed current transformers. Moving and stationary contacts are front accessible for simple and easy inspection and maintenance. All Class A200 starters are UL listed and recognized and are CSA certified.
Long Description	Eaton Freedom NEMA motor control starter, Non-Reversing Starter, 120V/60 Hz or 110V/50 Hz coil voltage, 90A, Three-pole, Size 3, 25 hp at 208V, 30 hp at 240V, 50 hp at 480,600V, A200 series, Wired for Separate Control
Product Type	Nema Size 3 Starter, 120VAC Coil, A200 S

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00786678231259
Manufacturers Part Number	A200M3CAC
UPC	786678231259

Taxonomies, Classifications, and Categories

Category Description	FULL VOLTAGE NON-REVERSING Control Starters
Type	Motor Control

Packaging

Carton	1
Weight Per each	9.8999



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Stationary Machinery and Equipment Outside Factory -

Stationary Machinery and Equipment Outside Factory - Other

standard

UL Listed, CSA Certified