



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



A36H2408SS6LP 36X24X8 N4X SS6 CH CLMP CVR

Hoffman Enclosures, Inc.

| | |
|------------------|--|
| Catalog Number | A36H2408SS6LP |
| Manufacturer | Hoffman Enclosures, Inc. |
| Description | Wallmount Hinged With Nema Clamps Type 4X, 36X24X8, Brushed, SS316 |
| Weight per unit | 69.0 (lbs/each) |
| Product Category | Nema Types 4 & 4X Metallic Enc |

Features

| | |
|-----------|----------------------|
| ip rating | IP66 |
| Material | Stainless Steel 316L |

Material, Color, and Finish

| | |
|--------|------------|
| Color | Unpainted |
| Finish | Brushed #4 |

Dimensions and Weight

| | |
|--------|---------------------|
| Depth | 8 |
| Height | 36 |
| Size | 30.00x24.00x8.00 in |
| Width | 24 |

Descriptions

| | |
|------------------------|--|
| Description | 36X24X8 N4X SS6 CH CLMP CVR |
| extra long description | NVENT HOF A36H2408SS6LP Stainless E |
| Features | For use in indoor and outdoor corrosive environments that require a water-tight seal, this enclosure's seamless foam-in-place gasket and screw-down clamps provide a secure seal against contaminants. |
| Long Description | Wallmount Hinged with NEMA Clamps Type 4X, 36x24x8, Brushed, SS316 |
| Product Type | Stainless Encl. 36.00X24.00X8. |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Nvent Hoffman |
| GTIN | 00783510836702 |
| Manufacturers Part Number | A36H2408SS6LP |
| UPC | 783510836702 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | STEEL JUNCTION BOXES |
| Type | Stainless Steel Wall Mounted Industrial Enclosures |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|----|
| Carton | 1 |
| Weight Per each | 69 |

Uses, Certifications, and Standards

| | |
|-------------|---|
| Application | Controls and Drives; Corrosive Environments |
| nema rating | 4X Watertight, corrosion-resistant |