



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ABMSAC 1.13" X 1.13" Nylon CBL Tie Adh Mount WHT *Panduit Corporation*

Catalog Number	ABMSAC
Manufacturer	Panduit Corporation
Description	Panduit'S Abms-A-C 2-Way Rubber-Based Adhesive Backed Cable Tie Mounts Have Been Designed For Fast Installation and Long-Term Performance and Reliability. They Are Made Of Nylon 6.6., and Can Be Used With Miniature, Intermediate, and Standard Cable Ties. Mounts Are 1.12" X 1.12" (28.5MM X 28.5MM), White In Color and Intended For Use In Indoor Environments. They Supplied In Strips Of 2 and Come In Packages Of 500.
Weight per unit	0.5100 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Polyamide (PA)
Material	Nylon 6.6
media	Yes
Screw Size	#6 (M3)
Temperature Range	-20°F - 120°F (-29°C - 49°C)

Material, Color, and Finish

Color	Natural
-------	---------

Descriptions

Description	1.13" X 1.13" NYLNL CBL TIE ADH MOUNT WHT
extra long description	PAN ABMS-A-C ABMS-A-C Cable Tie Mou
Long Description	Panduit's ABMS-A-C 2-way rubber-based adhesive backed cable tie mounts have been designed for fast installation and long-term performance and reliability. They are made of Nylon 6.6., and can be used with miniature, intermediate, and standard cable ties. Mounts are 1.12" x 1.12" (28.5mm x 28.5mm), white in color and intended for use in indoor environments. They supplied in strips of 2 and come in packages of 500.
Product Type	Abms-A-C Cable Tie Mount, Natural, Pa 6.6, Rubber Adh., 1.13

Manufacturer Information

Brand	PANDUIT
GTIN	00074983580026
Manufacturers Part Number	ABMS-A-C
UPC	074983580026



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie Mount

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Package	500
Weight Per each	0.51

Uses, Certifications, and Standards

Application	Indoor
Mounting	Adhesive Tape
Operating Temperature	120
standard	CE Compliant, UL Recognized: E136577, RoHS Compliant