



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ABMSAC 1.13" X 1.13" NylN CBL Tie Adh Mount WHT *Panduit Corporation*

Catalog Number	ABMSAC
Manufacturer	Panduit Corporation
Description	Panduit'S Abms-A-C 2-Way Rubber-Based Adhesive Backed Cable Tie Mounts Have Been Designed For Fast Installation and Long-Term Performance and Reliability. They Are Made Of Nylon 6.6., and Can Be Used With Miniature, Intermediate, and Standard Cable Ties. Mounts Are 1.12" X 1.12" (28.5MM X 28.5MM), White In Color and Intended For Use In Indoor Environments. They Supplied In Strips Of 2 and Come In Packages Of 500.
Weight per unit	0.5100 (lbs/each)
Product Category	Cable Ties & Wraps

Features

Cable Size	NA
Cable Type	Cable Tie Mount
insulation	Polyamide (PA)
Material	Nylon 6.6
media	Yes
Screw Size	#6 (M3)
Temperature Range	-20°F - 120°F (-29°C - 49°C)

Material, Color, and Finish

Color	Natural
-------	---------

Descriptions

Description	1.13" X 1.13" NYL N CBL TIE ADH MOUNT WHT
extra long description	PAN ABMS-A-C ABMS-A-C Cable Tie Mou
Long Description	Panduit's ABMS-A-C 2-way rubber-based adhesive backed cable tie mounts have been designed for fast installation and long-term performance and reliability. They are made of Nylon 6.6., and can be used with miniature, intermediate, and standard cable ties. Mounts are 1.12" x 1.12" (28.5mm x 28.5mm), white in color and intended for use in indoor environments. They supplied in strips of 2 and come in packages of 500.
Product Type	Abms-A-C Cable Tie Mount, Natural, Pa 6.6, Rubber Adh., 1.13

Manufacturer Information

Brand	PANDUIT
GTIN	00074983580026
Manufacturers Part Number	ABMS-A-C
UPC	074983580026



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type Cable Tie Mount

Availability

minimum qty 100

Packaging

Carton 100

Package 500

Weight Per each 0.51

Uses, Certifications, and Standards

Application Indoor

Mounting Adhesive Tape

Operating Temperature 120

standard CE Compliant, UL Recognized: E136577, RoHS Compliant